

MNX PC 150/35 LG



Sample photo

Order symbol: PC 150/35 LG
Product nbr: 6012313
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022134
EI. number:
 Finland: 3420343
 Denmark: 8212022124
 Italy: 7351070
 Sweden: 2535539
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	180	130	35	Ingress Protection (EN 60529): IP 66/67
inch:	7.1	5.1	1.4	Impact Resistance (EN 62262): IK 08

Materials:		Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 746C 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 6
Material:	Polycarbonate	
Base colour:	RAL 7035	
Cover colour:	RAL 7035	
Cover screws material:	Polyamide	
Cover screws colour:	Grey	
Gasket material:	TPE	

Temperatures:		Certificates: Germanischer Lloyd (GL) Underwriters Laboratories Det Norske Veritas Fimko Europe EN 62208: 2003 UL Canada Gost R
Short term:	-40 ... 120 °C	
Continuous:	-40 ... 80 °C	
Short term:	-40 ... 250 °F	
Continuous:	-40 ... 175 °F	

Accessories:	
MIV 150	Mounting plate (Galvanized steel)
MIN 10	DIN-15 Mounting rail
MIN 15	DIN-15 Mounting rail
MIV 10	DIN-35 Mounting rail
MIV 15	DIN-35 Mounting rail
FP A 150/180	Front plate (Aluminium)
HFP 180	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

