

MNX PC 150/85 XHG



Sample photo

Order symbol: PC 150/85 XHG
Product nbr: 6013333
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074061201
EI. number:
Finland: 3435602
Denmark: 8212027967
Sweden: 6013333
Norway:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

| Dimensions: | Length | Width | Height | Rating: |
|--------------|--------|-------|--------|---|
| mm: | 180 | 130 | 85 | Ingress Protection (EN 60529): IP 66/67 |
| inch: | 7.1 | 5.1 | 3.3 | Impact Resistance (EN 62262): IK 08 |

| Materials: | | Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 746C 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 6 |
|-------------------------------|---------------|---|
| Material: | Polycarbonate | |
| Base colour: | RAL 7035 | |
| Cover colour: | RAL 7035 | |
| Cover screws material: | Polyamide | |
| Cover screws colour: | Grey | |
| Gasket material: | PUR | |

| Temperatures: | | Certificates: |
|--------------------|----------------|---------------|
| Short term: | -40 ... 120 °C | |
| Continuous: | -40 ... 80 °C | |
| Short term: | -40 ... 250 °F | |
| Continuous: | -40 ... 175 °F | |

| Accessories: | |
|--------------|-----------------------------------|
| MIV 150 | Mounting plate (Galvanized steel) |
| MIN 10 | DIN-15 Mounting rail |
| MIN 15 | DIN-15 Mounting rail |
| MIV 10 | DIN-35 Mounting rail |
| MIV 15 | DIN-35 Mounting rail |
| FP A 150/180 | Front plate (Aluminium) |
| HFP 180 | Front plate hinge series |
| FP 22046 | Wall fastening lug (4 pcs) |

