

MNX PC 200/100 HG



Sample photo

Order symbol: PC 200/100 HG
Product nbr: 6011327
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022240
EI. number:
Finland: 3420373
Denmark: 8212022234
Italy: 7351125
Sweden: 2535572
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	255	180	100	Ingress Protection (EN 60529): IP 66/67
inch:	10.0	7.1	3.9	Impact Resistance (EN 62262): IK 08

Materials:		Rating:	
Material:	Polycarbonate	Electrical insulation: Totally insulated	
Base colour:	RAL 7035	Halogen free (DIN/VDE 0472, Part 815): Yes	
Cover colour:	RAL 7035	UV resistance: UL 508	
Cover screws material:	Polyamide	Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws colour:	Grey	Glow Wire Test (IEC 695-2-1) °C: 960	
Gasket material:	TPE	NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	

Temperatures:		Certificates:	
Short term:	-40 ... 120 °C	Germanischer Lloyd (GL)	
Continuous:	-40 ... 80 °C	Underwriters Laboratories	
Short term:	-40 ... 250 °F	Det Norske Veritas	
Continuous:	-40 ... 175 °F	Fimko	
		Europe EN 62208: 2003	
		UL Canada	
		Gost R	

Accessories:	
MIV 200	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIN 20	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
MIV 20	DIN-35 Mounting rail
FP A 200/180	Front plate (Aluminium)
HFP 180	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

