

**MNX PCM 100/60 G**



Sample photo

**Order symbol:** PCM 100/60 G  
**Product nbr:** 6016301  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074038005  
**EI. number:**  
Finland: 3421631  
Denmark: 8212027006  
Italy: 7341010  
Sweden: 2535303  
Norway: 2535501

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
<b>mm:</b>	130	80	60	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>	5.1	3.1	2.4	Impact Resistance (EN 62262): IK 08

Materials:		Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 746C 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 6
<b>Material:</b>	Polycarbonate	
<b>Base colour:</b>	RAL 7035	
<b>Cover colour:</b>	RAL 7035	
<b>Cover screws material:</b>	Polyamide	
<b>Cover screws colour:</b>	Grey	
<b>Gasket material:</b>	TPE	

Temperatures:		<b>Certificates:</b> Germanischer Lloyd (GL) Underwriters Laboratories Det Norske Veritas Fimko Europe EN 62208: 2003 UL Canada Gost R
<b>Short term:</b>	-40 ... 120 °C	
<b>Continuous:</b>	-40 ... 80 °C	
<b>Short term:</b>	-40 ... 250 °F	
<b>Continuous:</b>	-40 ... 175 °F	

Accessories:	
MIV 100	Mounting plate (Galvanized steel)
MIN 5	DIN-15 Mounting rail
MIN 10	DIN-15 Mounting rail
MIV 5	DIN-35 Mounting rail
MIV 10	DIN-35 Mounting rail
FP A 100/130	Front plate (Aluminium)
HFP 130	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

