

MNX PCM 200/150 T



Sample photo

Order symbol: PCM 200/150 T
Product nbr: 6016929
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074038333
EI. number:
 Finland: 3421678
 Denmark: 8212027394
 Italy: 7342080
 Sweden: 2535451
 Norway: 2535536

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	255	180	150	Ingress Protection (EN 60529): IP 66/67
inch:	10.0	7.1	5.9	Impact Resistance (EN 62262): IK 08

Materials:		Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 746C 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Material:	Polycarbonate	
Base colour:	RAL 7035	
Cover colour:	Smoked grey	
Cover screws material:	Polyamide	
Cover screws colour:	Black	
Gasket material:	TPE	

Temperatures:		Certificates: Germanischer Lloyd (GL) Underwriters Laboratories Det Norske Veritas Fimko Europe EN 62208: 2003 UL Canada Gost R
Short term:	-40 ... 120 °C	
Continuous:	-40 ... 80 °C	
Short term:	-40 ... 250 °F	
Continuous:	-40 ... 175 °F	

Accessories:	
MIV 200	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIN 20	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
MIV 20	DIN-35 Mounting rail
FP A 200/180	Front plate (Aluminium)
HFP 180	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

