

## Product OD-W02WB-24PD


based LEDs WB & BPE W2x4.6d color white


product-catalog	Based LEDs
color	white
part no.	OD-W02WB-24PD
voltage [V]	24-28
current [mA]	11-13
chromaticity coordinates	x 0.31/y 0.32
operating temperature [°C]	-25 +60
storage temperature [°C]	-30 +80

chip construction	GaN
luminous intensity typ. [mcd]	750 at 15 mA

## note

- all dimension are in millimeter
- $\bullet$  tolerance is  $\pm$  0.25 mm unless otherwise noted
- specifications are subject to change whithout notice
- version 1.0





© OSHINO LAMPS GmbH, Tennenloher Straße 19, D 90425 Nürnberg