

Product OD-G02Ba9R-24PD

based LEDs Ba9 Single Chip LED color green

product-catalog	based LEDs
color	green
part no.	OD-G02Ba9R-24PD
forward voltage [V] (DC)	24-28
current [mA] ±15%	16-19
wavelength [nm]	574
operating temperature [°C]	-25 +60
storage temperature [°C]	-30 +80


chip construction	InGaAlP
luminous intensity typ. [mcd]	100 at 15 mA

R = with reflector, which is standard. Protection Diode (PD) is standard in these lamps.

note

- all dimension are in millimeter
- tolerance is \pm 0.25 mm unless otherwise noted
- specifications are subject to change whithout notice
 version 1.0

© OSHINO LAMPS GmbH, Tennenloher Straße 19, D 90425 Nürnberg



25MAX

