

Product OD-W01Ba9R-24PD

based LEDs Ba9 Single Chip LED color white

product-catalog	based LEDs
color	white
part no.	OD-W01Ba9R-24PD
forward voltage [V] (DC)	24-28
current [mA] ±15%	15-19
chromaticity coordinates	x 0.31/y 0.32
operating temperature [°C]	-25 +60
storage temperature [°C]	-30 +80

chip construction	GaN
luminous intensity typ. [mcd]	3750 at 15 mA

R = with reflector, which is standard. Protection Diode (PD) is standard in these lamps.

note

- all dimension are in millimeter
- tolerance is \pm 0.25 mm unless otherwise noted
- specifications are subject to change whithout notice
- version 1.0

© OSHINO LAMPS GmbH, Tennenloher Straße 19, D 90425 Nürnberg



