



Sample photo

Order symbol: PCQ3 203612
Product nbr: 7035791
Description: Enclosure, PC
Remarks: Grey cover (quick-locking)

EAN: 6418074099372
EI. number:
Finland: 3424268

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	360	200	121	TRH 2036	DIN-35 Mounting rail
inch:	14.2	7.9	4.8	TF 28037	Wall fastening lug (4 pcs)
Materials:				TH A	Grey plastic hinges (2 pcs)
Material:	ABS			EU 3 QuickLock set 60	QuickLock screws (60 pcs)
Base colour:	Grey			MR 28036EU Set 60	Mounting screws (60 pcs)
Cover screws material:	Stainless steel			EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30
Cover colour:	Clear transparent			EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black
Gasket material:	Polyurethane			Rating:	
Temperatures:				Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (short term):	-40 ... 80 °C			Impact Resistance (EN 62262): IK07	
Temperature °C (continuous):	-40 ... 60 °C			Electrical insulation: Totally insulated	
Temperature °F (short term):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (continuous):	-40 ... 140 °F			Glow Wire Test (IEC 695-2-1) °C: 650	
Accessories:				Certificates:	
TM 2036	Mounting plate			SGS Fimko	
				Gost R	

