

Socket Terminals

<p>001</p>	<p>008</p>	<p>009</p>	<p>010</p>	<p>Terminal for Carrier use</p> <p>012</p>	<p>047</p>
<p>083</p>	<p>095 (soft brass)</p>	<p>250</p>	<p>117</p>	<p>for pitch 1,27mm/.050" & 1,50mm/.059"</p> <p>118</p>	
<p>for pitch 1,00mm/.039"</p> <p>172</p>	<p>for pitch 0,80mm/.031"</p> <p>174</p>	<p>for pitch 1,27mm/.050"</p> <p>148</p>	<p>for SMT pitch 1,27mm/.050" 1,50mm/.059" - 2,00mm/.079"</p> <p>119</p>	<p>for SMT pitch 1,00mm/.039"</p> <p>167</p>	<p>for SMT pitch 0,80mm/.031"</p> <p>169</p>
<p>for SMT use possible</p> <p>014</p>	<p>for SMT use possible</p> <p>016</p>	<p>for SMT use possible</p> <p>093</p>	<p>for SMT use possible</p> <p>144</p>	<p>for SMT use possible</p> <p>147</p>	<p>for SMT use possible</p> <p>157</p>
<h2>Wire Wrap Terminals</h2>					
<p>002</p>	<p>003</p>	<p>030 (Nail Head)</p>	<p>038</p>		