

Stranded wire Copper LSZH

Stranded Wires with LSZH Insulation, H07Z-K,
RND



FEATURES:

For use in pipes or ducts and internal wiring of appliances with maximum operating temperatures of 90°C

The cables produce no corrosive gases when burnt

Class 5 flexible copper conductor according to

BS EN 60228

SPECIFICATION:

Wire Code	H07Z-K
Cable type	Stranded
Shielding	unshielded
Conductor	Copper
Halogen-free	Yes
Conductor insulation	LSZH
Original packaging	100 m
Rated voltage	450/750 V
Temperature range	-25...+90 °C

PRODUCT RANGE:

Art. Nr.	Colour	Cross-section	ø Sheath
RND 475-00203	black	1.50 mm ²	3.5 mm
RND 475-00204	blue	1.50 mm ²	3.5 mm
RND 475-00205	brown	1.50 mm ²	3.5 mm
RND 475-00206	green/yellow	1.50 mm ²	3.5 mm
RND 475-00207	grey	1.50 mm ²	3.5 mm
RND 475-00208	red	1.50 mm ²	3.5 mm
RND 475-00209	white	1.50 mm ²	3.5 mm
RND 475-00210	yellow	1.50 mm ²	3.5 mm
RND 475-00211	orange	1.50 mm ²	3.5 mm
RND 475-00212	pink	1.50 mm ²	3.5 mm
RND 475-00213	violet	1.50 mm ²	3.5 mm
RND 475-00214	green	1.50 mm ²	3.5 mm
RND 475-00215	black	2.50 mm ²	4.3 mm
RND 475-00216	blue	2.50 mm ²	4.3 mm
RND 475-00217	brown	2.50 mm ²	4.3 mm
RND 475-00218	green/yellow	2.50 mm ²	4.3 mm
RND 475-00219	grey	2.50 mm ²	4.3 mm
RND 475-00220	red	2.50 mm ²	4.3 mm
RND 475-00221	white	2.50 mm ²	4.3 mm
RND 475-00222	yellow	2.50 mm ²	4.3 mm
RND 475-00223	orange	2.50 mm ²	4.3 mm
RND 475-00224	pink	2.50 mm ²	4.3 mm

Art. Nr.	Colour	Cross-section	∅ Sheath
RND 475-00225	violet	2.50 mm ²	4.3 mm
RND 475-00226	green	2.50 mm ²	4.3 mm
RND 475-00227	black	4.00 mm ²	4.9 mm
RND 475-00228	blue	4.00 mm ²	4.9 mm
RND 475-00229	brown	4.00 mm ²	4.9 mm
RND 475-00230	green/yellow	4.00 mm ²	4.9 mm
RND 475-00231	grey	4.00 mm ²	4.9 mm
RND 475-00232	red	4.00 mm ²	4.9 mm
RND 475-00233	white	4.00 mm ²	4.9 mm
RND 475-00234	yellow	4.00 mm ²	4.9 mm
RND 475-00235	violet	4.00 mm ²	4.9 mm
RND 475-00236	orange	4.00 mm ²	4.9 mm
RND 475-00237	pink	4.00 mm ²	4.9 mm
RND 475-00238	green	4.00 mm ²	4.9 mm
RND 475-00239	black	6.00 mm ²	5.5 mm
RND 475-00240	blue	6.00 mm ²	5.5 mm
RND 475-00241	brown	6.00 mm ²	5.5 mm
RND 475-00242	green/yellow	6.00 mm ²	5.5 mm
RND 475-00243	grey	6.00 mm ²	5.5 mm
RND 475-00244	red	6.00 mm ²	5.5 mm
RND 475-00245	white	6.00 mm ²	5.5 mm
RND 475-00246	yellow	6.00 mm ²	5.5 mm
RND 475-00247	violet	6.00 mm ²	5.5 mm
RND 475-00248	orange	6.00 mm ²	5.5 mm
RND 475-00249	pink	6.00 mm ²	5.5 mm