



Main

Range of product	Optiline
Cabling installation system	Trunking
Product or component type	Mini trunking
Product compatibility	Mini trunking

Complementary

Trunking material	Plastic
Compartment partitioning	1 compartment
Colour tint	White (RAL 9003)
Trunking dimension	12 x 20 mm
Fixing mode	Pre-punched fixing hole 100 mm Low voltage cable : bonding tape Power cable : screw-fixed
Material	PVC (polyvinyl chloride)
Quantity per set	42 m
Ambient air temperature for operation	-15...60 °C
Length	2100 mm
Height	20 mm
Width	12 mm

Environment

Standards	EN 50085-1 : 2005 EN 50085-2-1 : 2006 73/23/EEC
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant since 1434; Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.