



For Use With	CENTER-300,301,302,303
	Available for general condition, especially for complex and any place hard to reach.
Danga	-50°Cto 200°C -58°F to 392°F
Tolerances	±2.2°C or ±0.75% (±3.9°F or ±0.75%)
Туре	К

## **TP-K02** Immersion Probe



For Use With	CENTER-300,301,302,303
Applications	Available for temperature measurement of liquid, gels or air
Range	-50°Cto 700°C -58°F to 1292°F
Tolerances	±2.2°C or ±0.75% (±3.9°F or ±0.75%)
Туре	К

## **TP-K03** Surface Probe



For Use With	CENTER-300,301,302,303
Applications	Available for flat or curved surface measurement.
Range	-50°Cto 400°C -58°F to 752°F
Tolerances	±2.2°C or ±0.75% (±3.9°F or ±0.75%)
Туре	К

## **TP-K04** Piercing Probe

For Use With	CENTER-300,301,302,303	
Applications	Available for food service, liquids and gels measurement.	
Range	-50°Cto 600°C -58°F to 1122°F	
Tolerances	±2.2°C or ±0.75% (±3.9°F or ±0.75%)	
Туре	K	

## **TP-K05** Surface Probe

For Use With	CENTER-300,301,302,303	
Applications	Available for flat or curved surface or hard to reach surface measurement.	
Range	-50°Cto 400°C -58°F to 752°F	
Tolerances	±2.2°C or ±0.75% (±3.9°F or ±0.75%)	
Туре	К	