

# CM-05 DC/AC Current Probe



## FEATURES

- Accurate and High Resolution
- 23 mm Conductor Diameter
- One Touch Zero



## SPECIFICATION

Range	Output	Sensitivity	Accuracy
DCA 0-4A	DC 100mV/A	10mA/mVDC	+/- 2.0% +/- 0.005A
DCA 0-40A	DC 10mV/A	0.1A/mVDC	+/- 1.0% +/- 0.02A
DCA 0-150A	DC 1mV/A	1A/mVDC	+/- 1.0% +/- 0.2A
DCA 150-200A	DC 1mV/A	1A/mVDC	-2.2% +/- 0.2A
ACA 0-4A	AC 100mV/A	10mA/mVAC	+/- 2.0% +/- 0.003A
ACA 0-40A	AC 10mV/A	0.1A/mVAC	+/- 1.5% +/- 0.03A
ACA 0-150A	AC 1mV/A	1A/mVAC	+/- 1.5% +/- 0.3A
ACA 150-200A	AC 1mV/A	1A/mVAC	-2.2% +/- 0.3A

**Power Source:** 2 X 1.5V AA UM3 Batteries

**Current Consumption:** 8mA

**Operating Condition:** -10 °C to 50 °C at 85% max.

RH