




SEB 2630 S1,9 schwarz/black

Industrial Connectors:Measuring and Testing Equipment:Sockets:4 mm safety system

Product description	
Description	Safety built-in socket, 4 mm diameter, contact-protected, with 1.9 mm soldering spike, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Soldering spike can be soldered into printed boards. Accessory BES 1000. Installation hole: 12.2 mm diameter. Tightening torque: 50 Ncm.
Type	SEB 2630 S1,9 schwarz/black
Order No.	972 359-100
System	4 mm safety system
Housing Color	black
Other standard types	red color, order no. 972 359-101; blue color, order no. 972 359-102; yellow color, order no. 972 359-103; green color, order no. 972 359-104; yellow/green color, order no. 972 359-188



Technical data		
Type of contact	socket	
Type of termination	solder	
Standard	IEC 61010	
Rated voltage	AC/DC 1000 V	
Measurement Category	CAT II	
Rated current	24 A	

Contact resistance	5 mOhm
Mounting	screw
Material	
Contact material	brass
Contact surface material	gold-plated
Housing material	PA
Environmental conditions	
Temperature range	-40 °C to +80 °C
Inflammability class	
Housing	94 V-2