Air Suction Filter With One-touch Fittings Series **ZFB**

Features

SNC

One touch fittings for direct connection into vacuum lines.

- Easily replaceable elements.
- Inlet connector swivels to simplify piping.
- Mounting hole in body for attachment to machinery.

100

04

Compact and lightweight construction.

ZFB

Air suction filter with One-touch fittings





Replacement Element

Part no.	Applicable filter model			
I-34S-A	ZFB100			
I-35S-A	ZFB200			
I-36S-A	ZFB300			
Note) Spare elements are sold in packs of 10 pieces.				

 Basic type

 Tubing size
 Symbol
 Flow (k/min (ANR))

 Metric size
 100
 MAX.20

 (Release button: Blue
 200
 MAX.50

 300
 MAX.75

	IN/OUT applicable tubing O.D.							
	Size	Symbol	Tubing size	Applicable model				
		04	ø4	ZFB100				
	size	06	ø6	ZFB100				
	Metric si			ZFB200				
		08	ø8	ZFB200				
	Ź			ZFB300				
		10	ø10	ZFB300				

Specifications

How to order

Fluid	Air, Nitrogen	
Operating pressure	–100 to 0 kPa (No positive pressure)	
Withstand pressure	0.5 MPa	
Operating and ambient temperature range	0 to 60°C (No freezing)	
Filtration	30 µm	
Element differential pressure resistance	0.15 MPa	
Applicable tubing material	Nylon/Soft Nylon/Polyurethane	


Model

Tubing size	Model	Port size (Applicable tubing O.D.) IN side, OUT side	Recommended air flow (t/min (ANR))	Weight (g)
	ZFB100-04	ø4	10	22
	ZFB100-06	øó	20	22
Metric size	ZFB200-06	øó	30	30
Memic size	ZFB200-08	ø8	50	30
	ZFB300-08	ø8	75	39
	ZFB300-10	ø10	75	39





Series ZFB Air Suction Filter

ZFB Flow Characteristics



Dimensions





A D

OUT

5

£i

øJ

øL

E

0

ø4.2 hole

Ν

≥

øL



Page 1490