

## Miniature Fittings

# Series M

#### **Features**

- Compact piping space. The hose nipple has a large holding force, allowing easy connection and removal.
- A wide variety of models is available.

  Piping in the same direction is possible at different heights.
- Hose nipple, Hose elbow.

  Hose nipples and hose elbow accept nylon, soft nylon and polyurethane tubing.



Applicable tubing O.D.: Metric Size


Connecting thread: M3, M5, R1/8

#### **Specifications**

Applicable tubing material		Nylon	Soft nylon		Polyurethane
Applicable tubing	M3		ø3.18/ø2.18	ø4/ø2.5	ø2, ø3.18/ø2, ø4/ø2.5
	M5-R1/8	ø4/ø2.5 ø6/ø4		ø4/ø2.5 ø6/ø4	ø2, ø3.18/ø2 ø4/ø2.5, ø6/ø4
Max. operating pressure (at 20C)		1.5MPa	1.0MPa		0.8MPa
Connection size		M3, M5, R1/8			
Thread		JIS B0209 Class 2 (Metric thread), JIS B0203 (Taper thread for piping)			







Small tightening torque.

Secure sealing.

PAT.

With electroless nickel plated



#### **Miniature Fittings**

#### Series M5

D:	D 143		l 4 1	
Description	Remark(s)	Model	Appli	cation
Barb fittings for nylon tubing	ø4/2.5 X M5	M-5AN-4	To pipe nylon tubing.	
	ø6/4 X M5	M-5AN-6		
Barb fittings for soft tubing	ø2/1.2 X M5	M-5AU-2	To pipe polyurethane tubing.	
	ø3.18/2.18 X M5	- M-5AU-3	To pipe soft nylon tubing.	
	ø3.18/2 X M5		To pipe polyurethane tubing.	
	ø4/2.5 X M5	M-5AU-4	To pipe soft nylon, polyurethane tubing.	
	ø6/4 X M5	M-5AU-6		
Barb elbow for nylon tubing	ø4/2.5 X M5	M-5ALN-4	To pipe nylon tubing Body rotates 360° around the stud axis.	
	ø6/4 X M5	M-5ALN-6		an be fixed
Barb elbow for soft tubing	ø2/1.2 X M5	M-5ALU-2	Body rotates 360° around the stud axis. Position can be fixed after alignment.	polyurethane
	ø3.18/2.18 X M5	M-5ALU-3		
	ø3.18/2 X M5			polyurethane
	ø4/2.5 X M5	M-5ALU-4		
	ø6/4 X M5	M-5ALU-6		
Barb elbow for nylon tubing (H)	ø4/2.5 X M5	M-5ALHN-4	To pipe nylon tubing     Body rotates 360° around the stud axis.     Position can be fixed after alignment.	
	ø6/4 X M5	M-5ALHN-6		
Barb elbow for soft tubing (H)	ø3.18/2.18 X M5	A4.5AU.".		To pipe soft nylon tubing.
	ø3.18/2 X M5	M-5ALHU-3	360° around the stud axis. Position can be fixed after alignment.	To pipe polyurethane tubing.
	ø4/2.5 X M5	M-5ALHU-4		To pipe soft nylon, polyurethane
	ø6/4 X M5	M-5ALHU-6		tubing.
Bushing	R1/8 X M5 female	M-5B	Connection from R1/8 piping to M5 fittings.	
Plug		M-5P	To plug ur M5 port.	nused

_	55 1715						
	Description	Remark(s)	Model	Application			
	Hose nipple	ø4/2.5 X M5	M-5H-4	To pipe nylon, soft nylon, polyurethane			
	47	ø6/4 X M5	M-5H-6	tubing.			
	Hose elbow	ø4/2.5 X M5	M-5HL-4	• To pipe nylon, soft			
		ø6/4 X M5	M-5HL-6	nylon, polyurethane tubing. • Body rotates 360°			
	Hose elbow(H)	ø4/2.5 X M5	M-5HLH-4	around the stud axis. Position can be fixed			
		ø6/4 X M5	M-5HLH-6	after alignment.			
	Elbow	M5 female X M5 female	M-5L	Perpendicular piping.			
	Tee	M5 female X M5 female X M5 female	M-5T	Perpendicular piping in both directions.			
	Universal elbow	M5 female X M5 male	M-5UL	Body rotates 360° around the stud axis. Position can be fixed after alignment.			
	Universal tee	M5 female X M5 female X M5 male	M-5UT	Body rotates 360° around the stud axis. Position can be fixed after alignment.			
	Extension fitting	M5 male X M5 female	M-5J	For 3D piping to prevent interference between fittings.			
	Nipple	M5 male X M5 male	M-5N	To connect fittings and equipment or to connect 2 fittings.			
	Universal nipple	M5 male X M5 male PAT.	M-5UN	Body rotates 360° around the stud axis.			
	Bulkhead union	M5 X M5 female – female	M-5E	Panel mount connection			
	Bulkhead Reducer	Rc1/8 X M5 female	M-5ER	Reduction from Rc1/8 to M5. Panel mounting is possible.			
	Manifold	Rc1/8 X M5 female (9 port)	M-5M	Rc1/8 can be diverted in up to nine M5 stations. Panel mounting is possible.			
	Gasket	Material: SUS 304	M-5G1	M5 thread label			
	Gasket (H)	Material: Aluminium	M-5GH	M-5ALm-6 M-5ALHm-6 M-5HL-4, 6 M-5HLH-4, 6.			









### **Miniature Fittings**

## Series M3

## Series R1/8

			l	
Description	Remark(s)	Model		cation
Barb fittings for soft tubing	ø2/1.2 X M3	M-3AU-2	To pipe polyurethane tubing.	
	ø3.18/2.18 X M3	- M-3AU-3	To pipe soft nylon tubing.	
	ø3.18/2 X M3	WI-SAU-S	To pipe polyurethane tubing.	
	ø4/2.5 X M3	M-3AU-4	To pipe soft nylon, polyurethane tubing.	
Barb elbow for soft tubing	ø2/1.2 X M3	M-3ALU-2		To pipe polyurethane tubing.
	ø3.18/2.18 X M3	M-3ALU-3	360° around the stud axis. Position can be fixed after alignment.	To pipe soft nylon tubing.
	ø3.18/2 X M3			To pipe polyurethane tubing.
	ø4/2.5 X M3	M-3ALU-4		To pipe soft nylon, polyurethane tubing.
Universal elbow	M3 female X M3 male	M-3UL	Body rotates 360° around the stud axis. Position can be fixed after alignment.	
Universal tee	M3 female X M3 female X M3 male	M-3UT	Body rotates 360° around the stud axis. Position can be fixed after alignment.	
Nipple	M3 male X M3 male	M-3N	To connect fittings and equipment or to connect 2 fittings.	
Plug		M-3P	To plug ui M3 port.	nused
Gasket		M-3G	Sealant (Thread p	ortion)

D	D 1/1	A4 1.1	A 1: .:	
Description	Remark(s)	Model	Application	
Barb fittings for nylon tubing	ø4/2.5 X R1/8	M-01AN-4	To pipe	
	ø6/4 X R1/8	M-01AN-6	nylon tubing.	
Barb fittings for soft tubing	ø4/2.5 X R1/8	M-01AU-4	To pipe soft nylon, polyurethane	
	ø6/4 X R1/8	M-01AU-6	tubing.	
Hose nipple	ø4/2.5 X R1/8	M-01H-4	To pipe nylon, soft nylon, polyurethane	
	ø6/4 X R1/8	M-01H-6	tubing.	
Hose nipple	ø2/1.2 X 3.2 mm one-touch	M-32F-2	To pipe polyurethane	
	ø2/1.2 X 4 mm one-touch	M-04F-2	tubing.	
Plug-in reducer	ø2/1.2 X 3.2 mm	M-32R-2	To pipe polyurethane	
C	ø2/1.2 X 4 mm	M-04R-2	tubing.	