

# Material Content Declaration

## Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

We **Distrelec Group AG, Enterprise Hub, 7th Floor, 2 St Peter's Square Manchester, M2 3AA** hereby declare that the products listed below and described accordingly, do not contain any Substances deemed to be of Very High Concern (SVHC) above the threshold of 0.1% weight by weight. This declaration is made subject to the list of SVHCs published by the European Chemical Agency ([echa.europa.eu/candidate-list-table](http://echa.europa.eu/candidate-list-table)) at the date of issue of this declaration.

This declaration is made based on an analytical Test Results.

<b>RND ARTICLE NUMBER</b>	<b>RND PRODUCT DESCRIPTION</b>
RND 150CBB600.47UF450V	Motor Capacitor 50-60Hz M8 0.47µF 450V
RND 150CBB601.5UF450V	Motor Capacitor 50-60Hz M8 1.5µF 450V
RND 150CBB60100UF450V	Motor Capacitor 50-60Hz M8 100µF 450V
RND 150CBB60100UF450VCA	Motor Capacitor 50-60Hz M8 100µF 450V
RND 150CBB6010UF450V	Motor Capacitor 50-60Hz M8 10µF 450V
RND 150CBB60125UF450VCA	Motor Capacitor 50-60Hz M8 125µF 450V
RND 150CBB6012UF450V	Motor Capacitor 50-60Hz M8 12µF 450V
RND 150CBB6014UF450V	Motor Capacitor 50-60Hz M8 14µF 450V
RND 150CBB6015UF450V	Motor Capacitor 50-60Hz M8 15µF 450V
RND 150CBB6016UF450V	Motor Capacitor 50-60Hz M8 16µF 450V
RND 150CBB6018UF450V	Motor Capacitor 50-60Hz M8 18µF 450V
RND 150CBB601UF450V	Motor Capacitor 50-60Hz M8 1µF 450V
RND 150CBB602.5UF450V	Motor Capacitor 50-60Hz M8 2.5µF 450V
RND 150CBB602.5UF450VCA	Motor Capacitor 50-60Hz M8 2.5µF 450V
RND 150CBB6020UF450V	Motor Capacitor 50-60Hz M8 20µF 450V
RND 150CBB6025UF450V	Motor Capacitor 50-60Hz M8 25µF 450V
RND 150CBB602UF450V	Motor Capacitor 50-60Hz M8 2µF 450V
RND 150CBB603.5UF450V	Motor Capacitor 50-60Hz M8 3.5µF 450V
RND 150CBB6030UF450V	Motor Capacitor 50-60Hz M8 30µF 450V
RND 150CBB6035UF450V	Motor Capacitor 50-60Hz M8 35µF 450V
RND 150CBB603UF450V	Motor Capacitor 50-60Hz M8 3µF 450V
RND 150CBB603UF450VCA	Motor Capacitor 50-60Hz M8 3µF 450V
RND 150CBB604.5UF450V	Motor Capacitor 50-60Hz M8 4.5µF 450V
RND 150CBB6040UF450V	Motor Capacitor 50-60Hz M8 40µF 450V
RND 150CBB604UF450V	Motor Capacitor 50-60Hz M8 4µF 450V
RND 150CBB6050UF450V	Motor Capacitor 50-60Hz M8 50µF 450V
RND 150CBB605UF450V	Motor Capacitor 50-60Hz M8 5µF 450V
RND 150CBB605UF450VCA	Motor Capacitor 50-60Hz M8 5µF 450V
RND 150CBB606.3UF450V	Motor Capacitor 50-60Hz M8 6.3µF 450V
RND 150CBB6060UF450V	Motor Capacitor 50-60Hz M8 60µF 450V
RND 150CBB606UF450V	Motor Capacitor 50-60Hz M8 6µF 450V
RND 150CBB606UF450VCA	Motor Capacitor 50-60Hz M8 6µF 450V
RND 150CBB607.5UF450V	Motor Capacitor 50-60Hz M8 7.5µF 450V
RND 150CBB6070UF450V	Motor Capacitor 50-60Hz M8 70µF 450V
RND 150CBB6070UF450VCA	Motor Capacitor 50-60Hz M8 70µF 450V
RND 150CBB6080UF450V	Motor Capacitor 50-60Hz M8 80µF 450V
RND 150CBB6080UF450VCA	Motor Capacitor 50-60Hz M8 80µF 450V
RND 150CBB608UF450V	Motor Capacitor 50-60Hz M8 8µF 450V
RND 150CBB6090UF450VCA	Motor Capacitor 50-60Hz M8 90µF 450V
RND 150CBB608UF450VCA	Motor Capacitor 50-60Hz M8 8µF 450V



# Material Content Declaration

Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

RND 150CBB6010UF450VCA	Motor Capacitor 50-60Hz M8 10 $\mu$ F 450V
RND 150CBB6012UF450VCA	Motor Capacitor 50-60Hz M8 12 $\mu$ F 450V
RND 150CBB6016UF450VCA	Motor Capacitor 50-60Hz M8 16 $\mu$ F 450V
RND 150CBB6020UF450VCA	Motor Capacitor 50-60Hz M8 20 $\mu$ F 450V
RND 150CBB6025UF450VCA	Motor Capacitor 50-60Hz M8 25 $\mu$ F 450V
RND 150CBB602UF450VCA	Motor Capacitor 50-60Hz M8 2 $\mu$ F 450V
RND 150CBB6030UF450VCA	Motor Capacitor 50-60Hz M8 30 $\mu$ F 450V
RND 150CBB6040UF450VCA	Motor Capacitor 50-60Hz M8 40 $\mu$ F 450V
RND 150CBB604UF450VCA	Motor Capacitor 50-60Hz M8 4 $\mu$ F 450V
RND 150CBB6050UF450VCA	Motor Capacitor 50-60Hz M8 50 $\mu$ F 450V
RND 150CBB6060UF450VCA	Motor Capacitor 50-60Hz M8 60 $\mu$ F 450V

## DISTRELEC

Signed for and on behalf of:

---

David Connelly  
Senior Quality and Legislation Manager

Date 15/06/2020