


Prototyping Board



RE525-LF

- EPOXY fibre-glass FR4 1.5 mm single-sided 35 µm CU
- hot air leveling (HAL-leadfree)
- 37 x 57 single-hole conductor 2.1 mm Ø
- hole spacing 2.54 x 2.54 mm
- hole dia 1.0 mm
- connector 32-channel DIN 41612
- grid 5.08 mm type D
- size 100 x 160 mm