

CODES and COLOURS			INT.	REMOV.	WHEELS	INTERNAL DIMENSIONS (mm.)					EXT. DIMENSIONS (mm.)			WEIGHT	BUOYANCY	VOLUME
BLACK	ORANGE	GREEN	CONFIG.	LID		A	B	C	D	E	A	B	C	Kg.	*Kg.max	Litres
1908.B E	1908.O E	1908.G E	empty	---	---	190	125	85	20	65	216	180	102	0,70	1,4	2,0
1908.B	1908.O	1908.G	w/foam	---	---	190	125	85	20	65	216	180	102	0,80	---	---
1913.B E	1913.O E	1913.G E	empty	---	---	190	125	135	20	115	216	180	152	0,85	2,4	3,2
1913.B	1913.O	1913.G	w/foam	---	---	190	125	135	20	115	216	180	152	0,92	---	---
2209.B E	2209.O E	2209.G E	empty	---	---	220	160	95	20	75	246	215	112	0,88	2,3	3,3
2209.B	2209.O	2209.G	w/foam	---	---	220	160	95	20	75	246	215	112	0,99	---	---
2214.B E	2214.O E	2214.G E	empty	---	---	220	160	145	20	125	246	215	162	1,16	3,9	5,1
2214.B	2214.O	2214.G	w/foam	---	---	220	160	145	20	125	246	215	162	1,29	---	---
2712.B E	2712.O E	2712.G E	empty	YES	---	276	200	120	35	85	305	270	144	1,62	4,2	6,6
2712.B	2712.O	2712.G	w/foam	YES	---	276	200	120	35	85	305	270	144	1,83	---	---
2717.B E	2717.O E	2717.G E	empty	YES	---	276	200	170	35	135	305	270	194	1,93	6,7	9,3
2717.B	2717.O	2717.G	w/foam	YES	---	276	200	170	35	135	305	270	194	2,12	---	---
3317.B E	3317.O E	3317.G E	empty	YES	---	330	234	170	68	102	360	304	194	2,29	7,0	13,1
3317.B	3317.O	3317.G	w/foam	YES	---	330	234	170	68	102	360	304	194	2,51	---	---
3818.B E	3818.O E	3818.G E	empty	---	---	380	270	180	45	135	410	340	205	3,14	12,4	18,4
3818.B	3818.O	3818.G	w/foam	---	---	380	270	180	45	135	410	340	205	3,58	---	---
4412.B E	4412.O E	4412.G E	empty	YES	---	445	345	125	47	78	474	415	149	3,40	10,7	19,2
4412.B	4412.O	4412.G	w/foam	YES	---	445	345	125	47	78	474	415	149	3,90	---	---
4412.B C	-	4412.G C	computer case	YES	---	445	345	125	47	78	474	415	149	4,20	---	---
4419.B E	4419.O E	4419.G E	empty	YES	---	445	345	190	47	143	474	415	214	4,00	19,7	29,2
4419.B	4419.O	4419.G	w/foam	YES	---	445	345	190	47	143	474	415	214	4,70	---	---
4820.B E	4820.O E	4820.G E	empty	---	---	480	370	205	50	155	520	435	230	4,64	24,7	35,5
4820.B	4820.O	4820.G	w/foam	---	---	480	370	205	50	155	520	435	230	5,40	---	---
5117.B E	5117.O E	5117.G E	empty	YES	---	517	277	173	50	123	546	347	197	3,80	15,8	24,7
5117.B	5117.O	5117.G	w/foam	YES	---	517	277	173	50	123	546	347	197	4,50	---	---
5122.B E	5122.O E	5122.G E	empty	YES	YES	517	277	217	50	167**	546	347	247	6,00	21,5	31,0
5122.B	5122.O	5122.G	w/foam	YES	YES	517	277	217	50	167**	546	347	247	7,00	---	---
5822.B E	5822.O E	5822.G E	empty	---	---	580	440	220	60	160	650	510	242	6,96	36,7	56,1
5822.B	5822.O	5822.G	w/foam	---	---	580	440	220	60	160	650	510	242	8,19	---	---
5833.B E	5833.O E	5833.G E	empty	---	YES	580	440	330	60	270	682	510	355	9,55	62,0	84,2
5833.B	5833.O	5833.G	w/foam	---	YES	580	440	330	60	270	682	510	355	11,66	---	---
7630.B E	7630.O E	7630.G E	empty	---	YES	765	485	305	60	245	860	560	330	11,20	81,8	113,1
7630.B	7630.O	7630.G	w/foam	---	YES	765	485	305	60	245	860	560	330	14,03	---	---
7641.B E	7641.O E	7641.G E	empty	---	YES	765	485	415	60	355	860	560	435	12,07	118,5	153,9
7641.B	7641.O	7641.G	w/foam	---	YES	765	485	415	60	355	860	560	435	15,92	---	---
10840.B E	-	10840.G E	empty	YES	YES	1080	620	400	200	200	1178	718	427	19,80	120,6	260
10840.B E DL	-	-	empty+lock	YES	YES	1080	620	400	200	200	1178	718	427	20,20	---	---
10840.B	-	10840.G	w/foam	YES	YES	1080	620	400	200	200	1178	718	427	26,30	120,6	260
10840.B DL	-	-	w/foam+lock	YES	YES	1080	620	400	200	200	1178	718	427	26,70	---	---
10840.B D1	-	10840.G D1	int #1	YES	YES	1080	620	400	200	200	1178	718	427	---	120,6	260
10840.B D1 DL	-	-	int #1+lock	YES	YES	1080	620	400	200	200	1178	718	427	---	---	---
10840.B D2	-	10840.G D2	int #2	YES	YES	1080	620	400	200	200	1178	718	427	---	120,6	260
10840.B D2 DL	-	-	int #2+lock	YES	YES	1080	620	400	200	200	1178	718	427	---	---	---
11413.BE	-	11413.GE	empty	---	YES	1136	350	135	42	93	1189	415	159	7,80	33,3	53,7
11413.B	-	11413.G	w/foam	---	YES	1136	350	135	42	93	1189	415	159	8,80	---	---
11413.BEDL	-	-	empty+lock	---	YES	1136	350	135	42	93	1189	415	159	8,00	33,3	53,7
11413.BDL	-	-	w/foam+lock	---	YES	1136	350	135	42	93	1189	415	159	9,00	---	---
13513.BE	-	13513.GE	empty	---	YES	1350	350	135	42	93	1410	415	159	8,70	39,5	63,7
13513.B	-	13513.G	w/foam	---	YES	1350	350	135	42	93	1410	415	159	9,95	---	---
13513.BEDL	-	-	empty+lock	---	YES	1350	350	135	42	93	1410	415	159	8,90	39,5	63,7
13513.BDL	-	-	w/foam+lock	---	YES	1350	350	135	42	93	1410	415	159	10,15	---	---
13527.BE	-	13527.GE	empty	---	YES	1350	350	272	42	230	1430	415	296	11,70	97,5	128,5
13527.B	-	13527.G	w/foam	---	YES	1350	350	272	42	230	1430	415	296	14,90	---	---
13527.BEDL	-	-	empty+lock	---	YES	1350	350	272	42	230	1430	415	296	11,90	97,5	128,5
13527.BDL	-	-	w/foam+lock	---	YES	1350	350	272	42	230	1430	415	296	15,10	---	---