

Signal lamps with lamp socket - W 2 x 4.6d, 9.1 mm





Mounting hole

Technical Data

General information
Form of lens
Colour of lens
Diameter of collar

Dimensions
Dimensions
Description

Flow of the state o

Overall height 7 mm
Mounting depth 25.5 mm
Mounting hole 9.10 mm

Mechanical design
Mounting ring nut
Terminals solder/q

solder/quick connect terminals 2.8 x 0.8 mm

Lamp socket W 2 x 4.6d
Lamp filament lamp

Electrical characteristics

Voltage limit max. 35 V Power limit max. 1.2 W

Other specifications

Degree of protection from IP40 front side Weight 1 g


Typical accessories Signal lamps with lamp socket - W 2 x 4.6d, 9.1 mm

With Socket

Description	Photo	Order no.	Additional accessories see page
Filament lamp, W 2 x 4.6d base, 24 - 30 V	Tiby -	1.90.120.005/0000	5 - 4
Filament lamp, W 2 x 4.6d base, 60 V		1.90.120.009/0000	5 - 4
Filament lamp, W 2 x 4.6d base, 48 V	江山道一	1.90.120.010/0000	5 - 4
Filament lamp, W 2 x 4.6d base, 24 V	江山城一	1.90.120.011/0000	5 - 4
Filament lamp, W 2 x 4.6d base, 12 V	江山道一	1.90.120.012/0000	5 - 4
Fixing spanner M 9, M 10		5.58.002.025/0105	5 - 21



Signal lamps with lamp socket - W 2 x 4.6d, 9.1 mm, round lens



· · · · · · · · · · · · · · · · · · ·							
Voltage limit max.	Power limit max.	Lamp	Colour of lens	Order no. complete	Order no. single parts		
					Housing	Lens	
35 V	1.2 W	filament lamp	transparent colourless	1.66.001.011/1002	1.66.001.026/0000	5.49.255.002/1002	
35 V	1.2 W	filament lamp	transparent red	1.66.001.011/1301	1.66.001.026/0000	5.49.255.002/1301	
35 V	1.2 W	filament lamp	transparent yellow	1.66.001.011/1402	1.66.001.026/0000	5.49.255.002/1402	
35 V	1.2 W	filament lamp	transparent green	1.66.001.011/1502	1.66.001.026/0000	5.49.255.002/1502	
35 V	1.2 W	filament lamp	transparent blue	1.66.001.011/1601	1.66.001.026/0000	5.49.255.002/1601	

Technical data see page 3 - 44

Please order luminous elements separately.

With Socket