
STATECH SYSTEMS AG STS Alte Schmerikonerstrasse 3, CH-8733 Eschenbach SG / Switzerland www.statech.ch , sales@statech.ch			
Responsible: T. Buob	Date of 1. Issue: 15.09.2010 Version A: 09/2010	Technical data sheet N°: 1S1130	

Electrostatic Dissipative Rubber Floor Matting



Electrical properties (typical values)

Resistance to ground (R _G)	IEC 61340-5-1	< 1x 10 ⁹ Ω
Surface resistance (R _s)	IEC 61340-5-1	< 1x 10 ⁹ Ω
Walking Test	IEC 61340-4-5	< 10V

Mechanical properties (typical values)

Thickness		3mm
Abrasion	DIN 53 516	130 mm ³
Hardness	DIN 53 505	Shore A 80
Flammability	DIN 51960	flame resistant

Structure:

2 layer, synthetic rubber. Upper layer grey, dissipative; back layer black, conductive

Environmental sustainability:

Environment-friendly in all aspects. Does not contain any softening agents, formaldehydes, Asbestos or Cadmium (free of halogen). Does not generate poisonous or vitriolic vapours or gases in case of fire.

Disposal: recyclable. As domestic waste, on landfills or thermal recycling