



**FEATURES:**

Double tuning fork type contact guarantees high reliability.  
 2.0mm pitch Low-Profile mini type Match to 0.5mm SQ. posts.

**MATERIAL:**

- . Insulator.....30% Glass Filled P.B.T. (UL94V-0)
- . Contact.....Gold Plated
- . Terminal.....5191 Phosphor Bronze.

**SPECIFICATIONS**

- . Current Rating: 3 amperes Max.
- . Contact Resistance: 30MΩ Max.
- . Insulation Resistance: 1000megohms Max.
- . Dielectric Withstanding Voltage: AC 650 volts RMS at sea level

<div style="border: 2px solid black; padding: 5px; display: inline-block;"> <b>RoHS Compliant</b> </div>		<b>玄茂科技股份有限公司</b> <b>HSUAN MAO TECHNOLOGY CO., LTD.</b>	
		<b>PART NAME 品名</b> 2.0mm MINI JUMPER 2P H:3.5mm OPEN TYPE BLACK COLOR ROHS LOW-LEAD	
APPD. Angel		<b>TOLERANCE</b> .0 ± .00 ± ANG. ±	
DWG. Yumi	SCALE 参考	<b>SIZE.</b> A 4	
DATE 2009/11/30	UNIT M M	<b>REV.</b> A	
PAGE 1 OF 1	<b>PART NO. 料號</b> C9700-02AAXB00R		