



# 2-Port USB Cable KVM Switch

The CS22U is a 2-port USB Cable KVM Switch that provides a simple and quick method of selecting computers – a built-in remote port selector. This allows the CS22U unit to be hidden from sight, while the remote port selector can be placed conveniently on the desktop.

The CS22U's compact all-in-one design makes it ideal for multiplatform desktop applications that require high resolution video.

### **Petite**<sup>™</sup>



Setup



#### Features -----

- One USB console controls two USB computers
- Supports multifunction mice
- Multiplatform support Windows, Mac, Linux and Sun
- Superior video quality up to 2048 x 1536; DDC2B
- Non-powered

## Specifications ------

Function			CS22U
Computer Connections			2
Port Selection			Remote Port Selector
Connectors	Console Ports	Keyboard	1 x USB Type A Female (Black)
		Video	1 x HDB-15 Female (Blue)
		Mouse	1 x USB Type A Female (Black)
	KVM Ports	Keyboard/	2 x USB Type A Male
		Mouse	(Black)
		Video	2 x HDB-15 Male (Blue)
LEDs	Selected		2
Cable Length	Computers		0.9 m
	Remote Port Selector		1.8 m
Emulation	Keyboard / Mouse		USB
Video			2048 x 1536, DDC2B
Environment	Operating Temp.		0–50°C
	Storage Temp.		-20–60°C
	Humidity		0–80% RH,
			Non-condensing
Physical Properties	Housing		Plastic
	Weight		0.31 kg
	Dimensions (L x W x H)		8.24x7.71x2.46 cm

\* The specifications and pictures are subject to change without notice.



# Headquarters

ATEN International Co., Ltd. 3F, No.125, Sec. 2, Datung Rd. Sijhih City, Taipei 221, Taiwan Tel: 886-2-8692-6789 Fax: 886-2-8692-6767 E-mail: online@aten.com.tw

© Copyright 2009 ATEN® International Co., Ltd. All brand names and trademarks are the registered property of their respective owners