



The drawings contained herein are property of DATALOGIC S.p.A.
 Reproduction of this matter in whole or in part is forbidden without the express written consent of DATALOGIC S.p.A.

 LIPPO DI CALDERARA DI RENO BOLOGNA - ITALY WWW.DATALOGIC.IT	DESIGNER	DATE	SCALE	SHEET
	F. Franceschini	14-11-05	1/1	1/1
DENOMINATION	APPROV.	DATE	SCALE	SHEET
CAB-426 USB TYPE A, STRAIGHT	R. ROSSO			
PC BOARD	REV.			
CODE				
90A051945				
TYPE				
CAB-426				

NOTE: All materials employed have to be selected among RoHS compliant materials; the EC directives to be referred to are 2002/95/EC and correlated subsequent ones.



WIRE RUN LIST				
AWG	CONN 1	COLOR CABLE 1	CONN 2	FUNCTION
24	7	RED	1	VCC
	10	RED	1	VCC
28	3	WHITE	2	D -
	2	GREEN	3	D +
24	4	BLACK	4	GND
-	1.5	-	-	-
	-	DRAIN	SHELL	-

NOTE: CHECK 100% OF ELECTRICAL CONNECTIONS SUPPLIED

NOTES:
 1. TEST :
 INSUL. RESISTANCE : 20M0hm
 RESISTANCE VOLTAGE : 500V DC
 WITHSTAND VOLTAGE : AC/250V 2mA, FOR ONE MINUTE


- CABLE MAT-98 (-10°C~80°C OPERATING TEMPERATURE)
- CONN 1 RJ45 10 CONTACTS UNSHIELDED PHONE PLUG CONNECTOR, NOT KEYED, UL APPROVED
- CONN 2 USB A PLUG
- MN1 SLEEVE MA-32
- ET1 LABEL DAT 34-292

MN1 REALIZED WITH UL APPROVED INSULATING MATERIALS, COLOUR GRAY (RAL-7037), 65 +/-5 SHORE A HARDNESS

MN2 REALIZED WITH UL APPROVED INSULATING MATERIAL, COLOUR GRAY SURFACE (RAL-7037), HARDNESS WITHIN THE 65..75 A SHORE RANGE

NOTE:
 Each cable must be put in a plastic bag on which a label must be applied.
 The information on the label must be printed according to the following example.

CAB-426
 USB TYPE A, STRAIGHT



90A051945