



WEEE



RoHS compliant



EuP

EuP Complied

Switching Mode Power Supply

Input : 100-240V AC 50/60Hz for Worldwide Use

Model SMP-20WME



6 Output Setting



Model SMP-65WUSB

65Watt



Model SMP-30WME
Model SMP-45WUSB

45Watt

6 Output Setting



USB outlet port (female)



Features:

- Universal input voltage: 100-240V AC 50/60Hz for worldwide use
- Compact size and light
- Stabilized output, low ripple.
- Short circuit & overload protection
- High efficiency and low energy consumption
- Adjustable output voltages
- Power LED indicator
- SMP-20WME, SMP-30WME – For use with Radios, Calculators, Cassette recorders, Printers, telephones, CD/MD players and other battery operated appliances.
- SMP-45WUSB, SMP-65WUSB – For use with the most popular brands of Notebook and Netbook computers, mobile phones/ Mp3/ Mp4/ PDA/ iPod/ PSP...etc.

Model	Max. Current	DC output	Power LED Indicator	USB Port	AC Input plug			
					EU	UK	US	AUSTRALIA
SMP-20WME <i>Direct plug-in type</i>	2,5A	5/6V DC	✓		✓	✓	✓	✓
	2A	7,5V DC						
	1,7A	9/12V DC						
	1,5A	13,2V DC						
SMP-30WME	1,5A	9/12/15V DC	✓		✓	✓	✓	✓
	1,2A	18/20V DC						
	1A	24V DC						
SMP-45WUSB <i>Special design for use with Netbook</i> 45Watt	3,3A	9,5/12V DC	✓	✓	✓	✓	✓	✓
	2,5A	15V DC						
	2,1A	18/19V DC						
	2A	20V DC						
	1A	5V DC (USB outlet)						
SMP-65WUSB <i>Special design for use with Netbook & Notebook</i> 65Watt	4,5A	9,5/12V DC	✓	✓	✓	✓	✓	✓
	4A	15V DC						
	3,16A	18/19V DC						
	3A	20V DC						
	1A	5V DC (USB outlet)						

VANSON[®]

www.vanson.com.hk