





2-Port USB KVM Switch Kit with Audio TK-209K

The 2-Port USB Audio KVM Switch lets you control multimedia PCs with just one keyboard, monitor, mouse, microphone, and a set of speakers. The KVM switch not only allows you to share your monitor, keyboard and mouse but you can also share microphone and speakers. With just a simple press of a button, this KVM switch eliminates the hassle of cable swapping and switching between 2 PCs. With it's Hot-Plug, Auto-Scan and Hot-Key operating features, the TK-209K is the perfect choice for managing 2 PCs. Separate KVM cables are included.

FEATURES


- Use one keyboard, monitor, and mouse to control two computers
- 2-port USB KVM Switch with 1 set of Mic/Speaker port.
- 2 sets of VGA and 2 sets of Audio & Microphone Cables
- Supports Microsoft IntelliMouse, Optical Mouse, Logitech Net Mouse and more
- Supports super High Video Quality, up to 2048 x 1536 VGA resolution
- Supports Windows 98(SE)/ME/2000/XP/2003 Server, Linux, and Mac OS
- · Multi-Platform supports for PCs, Macintosh G3/G4, iMac and Mac Mini
- · Auto-Scan & LED display for PCs monitoring
- · Hot-Key, push button and Windows-based client switching software
- User definable hot-key (Windows Only)
- Plug & Play and Hot-Pluggable
- USB Interface Power method
- 2-Year Warrantv

2-Port USB KVM Switch Kit with Audio TK-209K

SPECIFICATIONS

Hardware		
Management	• 2 computers	
USB Interface	USB 1.1 Specifications Compliant	
KVM Cable	• 2 Sets of 1.2M (4ft) KVM Cables • 2 Sets of Audio/Microphone Cables (USB mini B to 3.5mm Jack)	
Cable Interface	KVM: To KVM: 1 x VGA/SVGA HDB 15-pin (male) To PC: 1 x USB (Type A), 1 x VGA/SVGA HDB 15-Pin (male)	
	 Audio: To KVM: 1 x USB (Mini B) To PC: 1 x 3.5mm audio in/out jack, 1 x 3.5mm microphone in/out jack 	
Console Connectors	• 1 x USB Keyboard (Type A) • 1 x USB Mouse (Type A) • 1 x VGA/SVGA HDB 15-pin	
	• 1 x 3.5mm audio in/out jack • 1 x 3.5mm microphone in/out jack	
Port Selection	Push Button, Hot-Key Commands, or Windows-Based Client Switching Software	
Auto-Scan Interval	• 10 ~ 60 seconds	
Keyboard State	Saved and Restored	
Power Type	USB Interface Power	
Dimensions	• 98 x 70 x 28 mm (3.86 x 2.76 x 1.1 in.)	
Weight	• 100 g (3.6 oz)	
Temperature	• Operating: 0°C ~ 40°C (32°F ~104°F); Storage: -20°C ~ 60°C (-4°F ~140°F)	
Humidity	• 0%~90%, Non-Condensing	
Certifications	• CE, FCC	

NETWORKING SOLUTIONS



PACKAGE CONTENTS

- TK-209K
- Multi-Language User's Guide
- Utility CD-ROM
- 2 sets of USB KVM Cables
- 2 sets of Audio/Mic Cables

RELATED PRODUCTS

TK-207K	2-Port USB KVM Switch
TK-208K	2-Port PS/2 Audio KVM Switch
TK-408K	4-Port PS/2 Audio KVM Switch Kit

ORDERING INFORMATION

TRENDNET[®]

20675 Manhattan Place, Torrance, CA 90501 USA

Tel: 1-310-961-5500 Fax: 1-310-961-5511 Web: www.trendnet.com Email: sales@trendnet.com

To Order Please Call:

1-888-326-6061

