

▶ Polycom® Communicator™ Model CX100

For Microsoft Office Communicator 2007



High quality, hands-free calls from your computer. Untie yourself from your headset with remarkable voice quality.

Polycom CX100 Speakerphone gives you the ultimate hands-free calling experience from your Microsoft Office Communicator 2007-enabled computer. Polycom CX100 Speakerphone enables crystal-clear, natural conversations without echoes or feedback. Enjoy the freedom of not wearing your headset for hands-free calls, or plug into the built-in stereo headphone port for private conversations.

Polycom CX100 Speakerphone delivers remarkable wideband audio quality that enables seamless voice and video communications with no compromises. Two high-quality microphones provide excellent range for small group conversations.

Polycom CX100 Speakerphone connects and powers through an integrated USB cable for easy installation and use – no extra cables to carry or batteries to charge. Its small size and carrying case make it easy to take with you. Plus, the high-fidelity speaker doubles as a great portable solution for CD-quality music and presentation audio.

The integrated button controls allow you to pick up or hang up calls, adjust speaker volume up and down, and mute the CX100's microphones during a call without using your mouse. LED indicators on the CX100 display various call states like incoming call, call muted, active call, and voicemail waiting for user.

Don't settle for imitators – only Polycom CX100 Speakerphone delivers a hands-free computer calling experience featuring:

- Remarkable voice quality
- Two high-quality microphones
- Integration with echo cancellation and other audio capabilities on Microsoft Office Communicator 2007 and the Microsoft Office Communication Server 2007
- Integrated button controls for a seamless user experience

Integrated with Microsoft Office Communicator 2007, Polycom CX100 Speakerphone is compatible with Windows XP®.

**Audio performance will vary by PC specification.*

Benefits

- ▶ **Hands-Free Freedom** – Untie yourself from your headset for clear one-on-one calls or group conversations
- ▶ **High-Fidelity Speaker** – High-quality audio for the best possible voice and video calls. Hardware supports up to 22kHz for CD-quality music or presentation audio
- ▶ **Two High-Quality Stereo Microphones** – Others on your call will hear every word clearly, whether you are in an office or a conference room
- ▶ **Easy to Use** – Convenient buttons enable you to launch applications, pick up and hang up calls, and control volume and mute
- ▶ **Built-in Stereo Headphone Port** – Plug in headphones for private conversations, or unplug to go hands-free
- ▶ **Ultimate Portability** – The integrated USB cable stores inside the unit for portability and convenience



Polycom® Communicator CX100 Specifications



Available in charcoal gray

Size

- 5.25 x 3.24 x 0.85 in
- (13.33 x 8.23 x 2.16 cm)
(L x W x H)

Weight

- 5.4 ounces (151 grams)

System Interface

- USB 1.1

Keypad

- Call Pick-up/Hang-up key
- Application Launch key
- Volume Up/Down keys
- Mute key
- LED light-ring for indication of call status

Loudspeaker

- Frequency response: 300 Hz to 19 KHz
- Volume: adjustable to 84 dBa (peak) volume at 0.5 meter

Microphones

- 2 cardioid microphones 200 Hz to 20 kHz

Auxiliary Audio Output

- 3.5 mm headphone jack for privacy
- Desktop PC speakers can be plugged in for audio pass-through
- Frequency response: 200 Hz to 22 kHz

Supported Applications

Polycom CX100 Speakerphone integrates with Microsoft Office Communicator 2007.



Untie yourself from your headset for one-on-one calls or small group conversations

Audio Enhancements

- Automatic Gain Control
- Dynamic Noise Reduction
- Gated microphones with intelligent switching

Minimum System Requirements

- Internet connection
- PC with 1 GHz processor
- 256 MB RAM
- 30 MB Hard disk space available for installation
- Windows® XP
- Compatible with select applications – visit www.polycom.com for more information
- One available USB connection

Recommended Room Conditions

- Reverberation time: <0.5 seconds
- Noise level: <48 dBa
- Approximate room size: 12 x 12 ft (3.7 x 3.7 meters)

Environmental Requirements

- Operating temperature: 40° 104°F (5° 40°C)
- Relative humidity: 20% 85% (noncondensing)
- Storage temperature: -22° 131°F (-30° 55°C)



Polycom Communicator model C100 works with Polycom PVX desktop video conferencing software and select IP soft phone applications.

Regulatory Compliance

- Approvals gained (Assessed to Class B EMC requirements)
 - FCC Part 15
 - ICES-003
 - CE
 - VCCI
 - GOST-R
 - C-Tick
 - CCC
 - CB/NRTL Safety
 - MIC
 - EN55024
 - EN61000-3-2
 - EN61000-3-3

Warranty

- 12 Months

Polycom Communicator Ships With:

- Polycom Communicator
- Integrated USB cable
- User guide
- Neoprene carry case

©2009 Polycom, Inc. All rights reserved.

Polycom and the Polycom logo design are registered trademarks of Polycom, Inc. in the U.S. and various countries.

All other trademarks are the property of their respective owners. Information in this document is subject to change without notice.



Polycom Headquarters
4750 Willow Road
Pleasanton, CA 94588
1.800.POLYCOM or
+1.925.924.6000

Polycom EMEA
270 Bath Road
Slough
Berkshire SL1 4DX
+44 (0)1753 723000

Polycom Asia Pacific
8 Shenton Way
#11-01 Temasek Tower
Singapore 068811
+65.6389.9200