# **Motor Driven Sirens**

## Super M



#### **Features**

- High output siren sound (127dB)
- Separate mounting bracket for easy installation
- Long life and run time
- Weatherproof for use both indoors and outdoors

#### Overview

The Super M is a powerful motor driven siren which emits a very high sound output. Designed for surface mounting, it has a separate mounting bracket which may be secured in position first to allow for easy installation. In addition, it comes pre-wired with 1 metre of cable.


It has a weatherproof construction when wall mounted and is suitable for continuous use.

The Super M is ideal for both security and fire applications where a higher sound output is required such as in areas of high background noise.

- Fire
- Security
- Industrial
- O Railway/Marine
- O Hazardous Area
- O Public Warning

### **Applications**

■ Fire alarm; security alarm; general safety warning; conveyors; process control alarm; vehicle alarm



Part No.	Colours	Audibility at 1m	Tones	Voltage	Current	
18-980047	Yellow	Up to 127 dB (A)	1	110V AC/DC	2.7A	
18-980049	Yellow	Up to 127 dB (A)	1	230V AC/DC	1.0A	

IP Rating: Weatherproof Rating: Continuous Frequency: 1680Hz Operating Temp: -30°C to +45°C Construction: ABS Cable Entries: 1 Weight: 1.8kg