



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

We Distrelec Group AG, Enterprise Hub, 7th Floor, 2 St Peter's Square Manchester, M2 3AA hereby declare that the products listed below and described accordingly, are manufactured such that, all constituent homogenous material does not contain the following substances at a concentration above 0.1% by weight. Where present, the value of Cadmium, as a concentration by weight, is 0.01%

- Lead
- Mercury
- Cadmium
- Hexavalent Chromium
- Polybrominated Biphenyls
- Polybrominated Diphenyl Ethers

In accordance with Clause 4.3.3 of standard EN 50581:2012, this declaration is made based on Analytical Test Results.

| RND ARTICLE NUMBER | RND PRODUCT DESCRIPTION |
|--------------------|--|
| RND 205-00622 | 2.54mm PIN HEADER 1X1P STRAIGHT TYPE GOL |
| RND 205-00623 | 2.54mm PIN HEADER 1X2P STRAIGHT TYPE GOL |
| RND 205-00624 | 2.54mm PIN HEADER 1X3P STRAIGHT TYPE GOL |
| RND 205-00625 | 2.54mm PIN HEADER 1X4P STRAIGHT TYPE GOL |
| RND 205-00626 | 2.54mm PIN HEADER 1X5P STRAIGHT TYPE GOL |
| RND 205-00627 | 2.54mm PIN HEADER 1X6P STRAIGHT TYPE GOL |
| RND 205-00628 | 2.54mm PIN HEADER 1X7P STRAIGHT TYPE GOL |
| RND 205-00629 | 2.54mm PIN HEADER 1X8P STRAIGHT TYPE GOL |
| RND 205-00630 | 2.54mm PIN HEADER 1X9P STRAIGHT TYPE GOL |
| RND 205-00631 | 2.54mm PIN HEADER 1X10P STRAIGHT TYPE GO |
| RND 205-00632 | 2.54mm PIN HEADER H=2.54mm 2X1P STRAIGHT |
| RND 205-00633 | 2.54mm PIN HEADER H=2.54mm 2X2P STRAIGHT |
| RND 205-00634 | 2.54mm PIN HEADER H=2.54mm 2X3P STRAIGHT |
| RND 205-00635 | 2.54mm PIN HEADER H=2.54mm 2X4P STRAIGHT |
| RND 205-00636 | 2.54mm PIN HEADER H=2.54mm 2X5P STRAIGHT |
| RND 205-00637 | 2.54mm PIN HEADER H=2.54mm 2X6P STRAIGHT |
| RND 205-00638 | 2.54mm PIN HEADER H=2.54mm 2X7P STRAIGHT |



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

| | |
|---------------|--|
| RND 205-00639 | 2.54mm PIN HEADER H=2.54mm 2X8P STRAIGHT |
| RND 205-00640 | 2.54mm PIN HEADER H=2.54mm 2X9P STRAIGHT |
| RND 205-00641 | 2.54mm PIN HEADER H=2.54mm 2X10 STRAIGHT |
| RND 205-00642 | 2.54mm FEMALE HEADER H:8.4mm 1X2P STRAIG |
| RND 205-00643 | 2.54mm FEMALE HEADER H:8.4mm 1X3P STRAIG |
| RND 205-00644 | 2.54mm FEMALE HEADER H:8.4mm 1X4P STRAIG |
| RND 205-00645 | 2.54mm FEMALE HEADER H:8.4mm 1X5P STRAIG |
| RND 205-00646 | 2.54mm FEMALE HEADER H:8.4mm 1X6P STRAIG |
| RND 205-00647 | 2.54mm FEMALE HEADER H:8.4mm 1X7P STRAIG |
| RND 205-00648 | 2.54mm FEMALE HEADER H:8.4mm 1X8P STRAIG |
| RND 205-00649 | 2.54mm FEMALE HEADER H:8.4mm 1X9P STRAIG |
| RND 205-00650 | 2.54mm FEMALE HEADER H:8.4mm 1X10P STRAI |
| RND 205-00651 | 2.54mm FEMALE HEADER H:8.4mm 2X2P STRAIG |
| RND 205-00652 | 2.54mm FEMALE HEADER H:8.4mm 2X3P STRAIG |
| RND 205-00653 | 2.54mm FEMALE HEADER H:8.4mm 2X4P STRAIG |
| RND 205-00654 | 2.54mm FEMALE HEADER H:8.4mm 2X5P STRAIG |
| RND 205-00655 | 2.54mm FEMALE HEADER H:8.4mm 2X6P STRAIG |
| RND 205-00656 | 2.54mm FEMALE HEADER H:8.4mm 2X7P STRAIG |
| RND 205-00657 | 2.54mm FEMALE HEADER H:8.4mm 2X8P STRAIG |
| RND 205-00658 | 2.54mm FEMALE HEADER H:8.4mm 2X9P STRAIG |
| RND 205-00659 | 2.54mm FEMALE HEADER H:8.4mm 2X10P STRAI |
| RND 205-00660 | USB A TYPE DIP TYPE 4P FEMALE 180° NICKE |
| RND 205-00661 | USB A TYPE DIP TYPE 4P FEMALE RIGHT ANGL |
| RND 205-00662 | 2.54mm HOUSING 1X2P WITH LOCKING RIBS BE |
| RND 205-00663 | 2.54mm HOUSING 1X3P WITH LOCKING RIBS BE |
| RND 205-00664 | 2.54mm HOUSING 1X4P WITH LOCKING RIBS BE |
| RND 205-00665 | 2.54mm HOUSING 1X5P WITH LOCKING RIBS BE |



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

| | |
|---------------|--|
| RND 205-00666 | 2.54mm HOUSING 1X6P WITH LOCKING RIBS BE |
| RND 205-00667 | 2.54mm HOUSING 1X7P WITH LOCKING RIBS BE |
| RND 205-00668 | 2.54mm HOUSING 1X8P WITH LOCKING RIBS BE |
| RND 205-00669 | 2.54mm HOUSING 1X9P WITH LOCKING RIBS BE |
| RND 205-00670 | 2.54mm HOUSING 1X10P WITH LOCKING RIBS B |
| RND 205-00671 | 2.54mm WAFER 2P STRAIGHT TYPE WITH LOCKI |
| RND 205-00672 | 2.54mm WAFER 3P STRAIGHT TYPE WITH LOCKI |
| RND 205-00673 | 2.54mm WAFER 4P STRAIGHT TYPE WITH LOCKI |
| RND 205-00674 | 2.54mm WAFER 5P STRAIGHT TYPE WITH LOCKI |
| RND 205-00675 | 2.54mm WAFER 6P STRAIGHT TYPE WITH LOCKI |
| RND 205-00676 | 2.54mm WAFER 7P STRAIGHT TYPE WITH LOCKI |
| RND 205-00677 | 2.54mm WAFER 8P STRAIGHT TYPE WITH LOCKI |
| RND 205-00678 | 2.54mm WAFER 9P STRAIGHT TYPE WITH LOCKI |
| RND 205-00679 | 2.54mm WAFER 10P STRAIGHT TYPE WITH LOCK |
| RND 205-00680 | IDC SOCKET 2.54mm X 2.54mm 6P WITH S/R W |
| RND 205-00681 | IDC SOCKET 2.54mm X 2.54mm 8P WITH S/R W |
| RND 205-00682 | IDC SOCKET 2.54mm X 2.54mm 10P WITH S/R |
| RND 205-00683 | IDC SOCKET 2.54mm X 2.54mm 12P WITH S/R |
| RND 205-00684 | IDC SOCKET 2.54mm X 2.54mm 14P WITH S/R |
| RND 205-00685 | IDC SOCKET 2.54mm X 2.54mm 16P WITH S/R |
| RND 205-00686 | IDC SOCKET 2.54mm X 2.54mm 18P WITH S/R |
| RND 205-00687 | IDC SOCKET 2.54mm X 2.54mm 20P WITH S/R |
| RND 205-00688 | DIP PLUG 2.54mm X 2.54mm 6P SELECTIVE GO |
| RND 205-00689 | DIP PLUG 2.54mm X 2.54mm 8P SELECTIVE GO |
| RND 205-00690 | DIP PLUG 2.54mm X 2.54mm 10P SELECTIVE G |
| RND 205-00691 | DIP PLUG 2.54mm X 2.54mm 12P SELECTIVE G |
| RND 205-00692 | DIP PLUG 2.54mm X 2.54mm 14P SELECTIVE G |



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

| | |
|---------------|--|
| RND 205-00693 | DIP PLUG 2.54mm X 2.54mm 16P SELECTIVE G |
| RND 205-00694 | DIP PLUG 2.54mm X 2.54mm 18P SELECTIVE G |
| RND 205-00695 | DIP PLUG 2.54mm X 2.54mm 20P SELECTIVE G |
| RND 205-00696 | 2.54mm Terminal Brass Tin plated awg22-2 |

DISTRELEC

Signed for and on behalf of:

16/5/19

Thomas Westcott
Head of Quality and Legislation

Date