



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

We Distrelec Group AG, Enterprise Hub, 7th Floor, 2 St Peter's Square Manchester, M2 3AA hereby declare that the products listed below and described accordingly, are manufactured such that, all constituent homogenous material does not contain the following substances at a concentration above 0.1% by weight. Where present, the value of Cadmium, as a concentration by weight, is 0.01%

- Lead
- Mercury
- Cadmium
- Hexavalent Chromium
- Polybrominated Biphenyls
- Polybrominated Diphenyl Ethers

In accordance with Clause 4.3.3 of standard EN 50581:2012, this declaration is made based on Analytical Test Results.

RND Article Number	RND PRODUCT DESCRIPTION
RND 165-00001	FERRITE CORE SPLIT 6.5MM 220 OHM
RND 165-00002	FERRITE CORE SPLIT 13MM 150 OHM
RND 165-00003	FERRITE CORE SPLIT 12.7MM
RND 165-00004	FERRITE CORE SPLIT 5MM 115OHM
RND 165-00005	FERRITE CORE SPLIT 13MM 150 OHM
RND 165-00006	FERRITE CORE SPLIT 5.5MM 168OHM
RND 165-00007	FERRITE CORE SPLIT 8.5MM 204OHM
RND 165-00008	FERRITE CORE SPLIT 4.9MM 180 OHM
RND 165-00009	FERRITE CORE SPLIT 10.5MM
RND 165-00010	FERRITE CORE SPLIT 3.8MM 121OHM
RND 165-00011	FERRITE CORE SPLIT 12.5MM
RND 165-00012	FERRITE CORE SPLIT 5MM 182OHM
RND 165-00013	FERRITE CORE SPLIT 10.5MM
RND 165-00014	FERRITE CORE SPLIT 8.5MM 241OHM
RND 165-00015	FERRITE CORE SPLIT 8MM 246OHM
RND 165-00016	FERRITE CORE SPLIT 5MM 182OHM
RND 165-00017	FERRITE CORE CYLINDRICAL 160 OHM



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

RND 165-00018	FERRITE CORE CYLINDRICAL 210 OHM
RND 165-00019	FERRITE CORE CYLINDRICAL 200 OHM
RND 165-00020	FERRITE CORE CYLINDRICAL 128 OHM
RND 165-00021	FERRITE CORE CYLINDRICAL 220 OHM
RND 165-00022	FERRITE CORE CYLINDRICAL 225OHM
RND 165-00023	FERRITE CORE CYLINDRICAL 85OHM
RND 165-00024	FERRITE CORE CYLINDRICAL 250 OHM
RND 165-00025	FERRITE CORE CYLINDRICAL 110 OHM
RND 165-00026	FERRITE CORE CYLINDRICAL 75OHM
RND 165-00027	FERRITE CORE CYLINDRICAL 568OHM
RND 165-00028	FERRITE CORE CYLINDRICAL 200 OHM
RND 165-00029	FERRITE CORE CYLINDRICAL 501OHM
RND 165-00179	Ferrite Core, 1.5mm, 51 Ohm@100MHz
RND 165-00180	Ferrite Core, 2mm, 42 Ohm@100MHz
RND 165-00181	Ferrite Core, 4.5mm, 94 Ohm@100MHz
RND 165-00182	Ferrite Core, 5mm, 59 Ohm@100MHz
RND 165-00183	Ferrite Core, 5mm, 60 Ohm@100MHz
RND 165-00184	Ferrite Core, 5.5mm, 115 Ohm@100MHz
RND 165-00185	Ferrite Core, 5.6mm, 224 Ohm@100MHz
RND 165-00186	Ferrite Core, 7mm, 92 Ohm@100MHz
RND 165-00187	Ferrite Core, 7mm, 180 Ohm@100MHz
RND 165-00188	Ferrite Core, 16mm, 145 Ohm@100MHz
RND 165-00189	Ferrite Split, 4.5mm, 55 Ohm@100MHz
RND 165-00190	Ferrite Split, 4.5mm, 40 Ohm@100MHz
RND 165-00191	Ferrite Split, 4.5mm, 45 Ohm@100MHz
RND 165-00192	Ferrite Split, 4.5mm, 105 Ohm@100MHz
RND 165-00193	Ferrite Toroidal Core 50x32



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

RND 165-00194	Ferrite Toroidal Core 27x14.5
RND 165-00195	Ferrite Toroidal Core 35.6x23
RND 165-00196	Ferrite Toroidal Core 22.2x13.8
RND 165-00197	Ferrite Toroidal Core 14x8.7
RND 165-00198	Ferrite Toroidal Core 21x13.2
RND 165-00199	Ferrite Toroidal Core 61.4x36
RND 165-00200	Ferrite Toroidal Core 12.7x7.9
RND 165-00201	Ferrite Toroidal Core 29x19
RND 165-00202	Ferrite Toroidal Core 35.6x23
RND 165-00203	Ferrite Toroidal Core 35.6x23
RND 165-00204	Ferrite Toroidal Core 25x15
RND 165-00205	Ferrite Toroidal Core 16x9
RND 165-00206	Ferrite Toroidal Core 10x6
RND 165-00207	Ferrite Toroidal Core 35.6x23
RND 165-00208	Ferrite Toroidal Core 29x19
RND 165-00209	Ferrite Toroidal Core 12.7x7.9
RND 165-00210	Ferrite Toroidal Core 20x10
RND 165-00211	Ferrite Toroidal Core 18x8.5
RND 165-00212	Ferrite Toroidal Core 25x15
RND 165-00213	Ferrite Toroidal Core 36x23
RND 165-00214	Ferrite Toroidal Core 16x9.6
RND 165-00215	Ferrite Toroidal Core 10x6
RND 165-00216	Ferrite Toroidal Core 6x3
RND 165-00217	Ferrite Toroidal Core 10x6
RND 165-00218	Ferrite Toroidal Core 12.7x7.3
RND 165-00179	Ferrite Core, 1.5mm, 51 Ohm@100MHz
RND 165-00180	Ferrite Core, 2mm, 42 Ohm@100MHz



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

RND 165-00181	Ferrite Core, 4.5mm, 94 Ohm@100MHz
RND 165-00182	Ferrite Core, 5mm, 59 Ohm@100MHz
RND 165-00183	Ferrite Core, 5mm, 60 Ohm@100MHz
RND 165-00184	Ferrite Core, 5.5mm, 115 Ohm@100MHz
RND 165-00185	Ferrite Core, 5.6mm, 224 Ohm@100MHz
RND 165-00186	Ferrite Core, 7mm, 92 Ohm@100MHz
RND 165-00187	Ferrite Core, 7mm, 180 Ohm@100MHz
RND 165-00188	Ferrite Core, 16mm, 145 Ohm@100MHz
RND 165-00189	Ferrite Split, 4.5mm, 55 Ohm@100MHz
RND 165-00190	Ferrite Split, 4.5mm, 40 Ohm@100MHz
RND 165-00191	Ferrite Split, 4.5mm, 45 Ohm@100MHz
RND 165-00192	Ferrite Split, 4.5mm, 105 Ohm@100MHz
RND 165-00193	Ferrite Toroidal Core 50x32
RND 165-00194	Ferrite Toroidal Core 27x14.5
RND 165-00195	Ferrite Toroidal Core 35.6x23
RND 165-00196	Ferrite Toroidal Core 22.2x13.8
RND 165-00197	Ferrite Toroidal Core 14x8.7
RND 165-00198	Ferrite Toroidal Core 21x13.2
RND 165-00199	Ferrite Toroidal Core 61.4x36
RND 165-00200	Ferrite Toroidal Core 12.7x7.9
RND 165-00201	Ferrite Toroidal Core 29x19
RND 165-00202	Ferrite Toroidal Core 35.6x23
RND 165-00203	Ferrite Toroidal Core 35.6x23
RND 165-00204	Ferrite Toroidal Core 25x15
RND 165-00205	Ferrite Toroidal Core 16x9
RND 165-00206	Ferrite Toroidal Core 10x6
RND 165-00207	Ferrite Toroidal Core 35.6x23



Material Content Declaration

Restriction of Hazardous Substances (RoHS)

RND 165-00208	Ferrite Toroidal Core 29x19
RND 165-00209	Ferrite Toroidal Core 12.7x7.9
RND 165-00210	Ferrite Toroidal Core 20x10
RND 165-00211	Ferrite Toroidal Core 18x8.5
RND 165-00212	Ferrite Toroidal Core 25x15
RND 165-00213	Ferrite Toroidal Core 36x23
RND 165-00214	Ferrite Toroidal Core 16x9.6
RND 165-00215	Ferrite Toroidal Core 10x6
RND 165-00216	Ferrite Toroidal Core 6x3
RND 165-00217	Ferrite Toroidal Core 10x6
RND 165-00218	Ferrite Toroidal Core 12.7x7.3

Signed for and on behalf of:

DISTRELEC

A handwritten signature in blue ink, appearing to read 'T. Westcott'.

A handwritten date in blue ink, '24/2/19'.

Thomas Westcott
Head of Quality and Legislation

Date

