

Li-Ion Battery H2B178

- 3.6 V, 1.88 Ah
- Integrated Protection Circuit
- Soft pack
- 10 cm wire



Specification

General	
Configuration	1S1P
Nominal voltage	3.7 V
Nominal capacity	1880 mAh
Watt-hour rating	6.95 Wh
Standard charging	3.7 V, 1.316 A, 3 h, 25°C (Constant voltage, constant current)
Standard discharging	1.88 A (Constant current, 3.0 V end, 25°C)
Continuous allowable discharging current	2 A
Cell	
Type	Sanyo UF103450P
Typical capacity	1880 mAh
Safety protection board	
Cut off voltage	4.07 V
End of discharge voltage	2.3 V
Over current detection	3.2 A
Environmental	
Operating temperature range	Standard charging 0..45°C
	Quick charging 10..45°C
	Standard discharging -20..70°C
Physical	
Dimensions	53 x 34 x 10.6 mm
Weight	0.050 kg
Connection	2 wires 10 cm

Li-Ion Battery H2B178

Dimensions

