
Indicators with LED LED Indicators, 8 mm Panel Cutout







FEATURES:

For panel thicknesses 0.5-3.5 mm, panel cut-out 8 mm diameter

Supplied with nut and spring washer

SPECIFICATION:

Current	10 mA	
Flush-mounted ø	8 mm	
LED diameter	3.2 mm	
Termination type	Pin Connections	
Material	Chromium-plated brass	
Dimensions ø x L	10 x 17 mm	
Temperature range	+80 °C	

PRODUCT RANGE:

Art. Nr.	Light colour
RND 210-00014	amber
RND 210-00013	red