Hirschmann Automation and Control GmbH






AGS 20

Industrial Connectors:Measuring and Testing Equipment:Alligator clips:4 mm system

d steel alligator clip. Clamping range up to a maximum bolt diameter 5 diameter socket connection, connection possible by terminal screw and ection.
1
m



Technical data	
Type of contact	socket
Type of termination	4 mm socket, solder, screw
Rated voltage	DC 60 V
Contact resistance	10 mOhm
Material	
Contact material	steel
Contact surface material	nickel-plated
Housing material	steel
Environmental conditions	
Temperature range	-25 °C to +100 °C
Inflammability class	
Housing	94 HB