
# Push Buttons & Operator Interface - XAL Control Stations Dimensions

#### Single-way control stations XALD1., K1., D01



- 2 knock-outs for PG 13.5 cable glands, maximum capacity 0.47 in (12 mm).
- (2) Knock-out for cable entry, maximum capacity 0.55 in (14 mm).


#### Examples:

2.09 53


(3) (4) (9)

- (3) 2.44 in (62 mm) for flush push buttons.
- (4) 2.59 in (66 mm) for projecting push buttons.
- (5) 3.58 in (91 mm) for latching mushroom head push buttons.
- (6) 2.91 in (74 mm) for key switches.
- (7) 4.45 in (113 mm) for latching mushroom head push buttons with key release.
- (8) 3.78 in (96 mm) for key switches with key.
- (9) 2.52 in (64 mm) for pilot lights.


#### Two-way control stations XALD2., K2., D02




### Three-way control stations XALD3\*\*, K3\*\*, D03



#### Four-way control stations XALD4., K4., D04



## Five-way control stations XALD5••, K5••, D05



- Examples:
- (3) 2.44 in (62 mm) for flush push buttons.

maximum capacity 0.47 in (12 mm).

Knock-out for cable entry, maximum capacity 0.55 in (14 mm).

- (4) 2.59 in (66 mm) for projecting push buttons.
- (5) 2.52 in (64 mm) for pilot lights.
- (6) 3.43 in (87 mm) for mushroom head push buttons.
- (7) 3.07 in (78 mm) for selector switches.

Dual Dimensions inches mm