3M[™] Pak 100 Wiremount Socket .100" × .100" for .050" Pitch Cable (Optional Plastic or Metal Strain Relief) 3000 Series



- Industry standard IDC socket
- Optional plastic or low profile metal strain relief
- Positive locking metal "J" clips provide high cover retention
- Mates with 3M headers, plugs and pin strips for quick connect/disconnect capability
- Open or closed end covers available
- Accepts flat cable or discrete wire
- Military polarization, with or without centerbump

Date Modified: May 17, 2004

TS-0718-07 Sheet 1 of 2

Physical

InsulationMaterial:Glass Filled Polyester (PBT)Flammability:UL 94V-0Color:GrayContactCopper AlloyMaterial:Copper AlloyPlating100 μ'' [2.54 μ m] Nickel — QQ-N-290, Class 2Wiping Area:30 μ'' [0.76 μ m] Gold — MIL-G-45204, Type II, Grade CWire Accommodation:26 & 28 AWG Solid or StrandedMarking:3M Logo, Part Identification Number and Orientation Triangle

Electrical


Current Rating:1 AInsulation Resistance:> $1 \times 10^9 \Omega$ at 500 VdcWithstanding Voltage:1000 Vrms at Sea Level

Environmental

Temperature Rating: -55°C to +105°C

UL File No.: E68080

3M[™] Pak 100 Wiremount Socket .100" × .100" for .050" Pitch Cable (Optional Plastic or Metal Strain Relief) 3000 Series



3M Interconnect Solutions http://www.3M.com/interconnects/

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



Electronic Solutions Division

6801 River Place Blvd. Austin, TX 78726-9000 www.3M.com/esd

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 1 year from the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**