Product Information

2477PJO075P30

EAN 4031582050363

Swivel castor with total lock, tail end of caster, Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey nonmarking, plain bearing, bolt hole

Castors can be mounted with standard screws; various length screws can be used..

Option:

This castor is also in electric conductive version available. Please replace PJO with YGO when ordering..

Wheel diameter	75 mm
Width of Tread	25 mm
Centre hole	11 mm
Offset	24 mm
Swivel Interference	160 mm
Overall height	100 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.266 Kg / daN
Dynamic Load capacity	75 Kg / daN
Static Load capacity	150 Kg / daN
Hardness of tread	A 87 Shore



Versions:





