# 19" CABINETS

#### **Attachment Set**



- Nickel-plated M6 x 15mm locking bolt with combi slotted/pozi head, PA washer, M6 caged nut with stainless-steel cage
- Pack of 44

TYPE NO CAX000001 **SDESCRITPTION** 

HEAVY DUTY ENCLOSURES

HAND HELD CASES

DIN RAIL BOXES

#### **Front Guides Mounting**



• Attached to rack by two anchoring points with M6 bolts.

- · Made of steel, 2mm thick
- · Zinc plated coating
- 1 Pair of guides and assembly hardware

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

TYPE NO.

SDESCRITPTION

CAXFMG001

Front guide Mounting

### LX Wheel Kit



- Set of 4 double rotating wheels with rubber rolling band or polyamide.
- · Bracket made of stamped steel, with double roll of balls
- Maximum dynamic load acceptable per set: 2.400N/240 Kg (Standard), 3200N/320 Kg. (Heavy duty), and 800N/80 Kg (CamRack-QX)

POTTING BOXES

DESKTOP &

INSTRUMENT CASES

TYPE NO. DESCRITPTION CLX000001 LX Wheel Kit

## 19" ENCLOSURES

19" SUBRACKS

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES

#### **Cable Guides Clamps**

- Manufactured in steel
- · Standard finish: Epoxy paint simillar to RAL 9004
- Pack quantity x1

TYPE NO.	DESCRITPTION
CAX19CGC1	1U Guide
CAX19CGC2	2U Guide

### **Clip-on Support Guides**


- · Made of steel. 2mm thick
- · Quick attachment to the rack, without bolts
- · Zinc plated coated
- 1 pair of guides, 4 stoppers

TYPE NO.	DEPTH
CAXCSG345	345mm
CAXCSG545	545mm



We operate a constant improvement policy. our products are subject to change without notice





# 19" CABINETS

#### **Side Mount Tray**



TYPE NO.	WIDTH	DEPTH
CAXSMT350	424mm	350mm

- Manufactured in steel, 1.5mm thick.
- Easy assembly, attached to the rack at four anchoring points with M6 bolts
- Attachment points adaptable to variations in the depth of the 19" sections
- Recommended maximum static load: 60 Kg
- · Standard ventilation slots
- · Colour epoxy paint, anthracite
- One tray with mounting hardware

#### **Cantilever Tray**

TYPE NO.	U	DEPTH
CAX2TY180	2U	180mm
CAX2TY280	2U	280mm
CAX2TY350	2U	350mm
CAX2TY400	2U	400mm



- Manufactured in steel, 1.5mm thick.
- 19" assembly with four anchoring points on the front sections
- Recommended maximum static load: 10/20 Kg
- · Standard ventilation slots
- Front fastening height 2U
- One tray with mounting hardware
- Standard depths 180, 280, 350, 400mm
- Grey graphite expoxy paint, anthracite
- 1 tray (screws not included)

UNIVERSAL ENCLOSURES

> HAND HELD CASES

HEAVY DUTY ENCLOSURES

> DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

> 19" SUBRACKS

CUSTOM SIZED ENCLOSURES

> CUSTOM SERVICES