# PRODUCT DATASHEET

### Value Metal



BRIGHT

• Five LEDs provide 35 lumens



### HANDY

 Easy to operate pushbutton tailcap switch



634041

European Region

Lightweight and compact, the Energizer Value Metal torch is an economical general lighting choice. It has an aluminum body and an easy to operate pushbutton tailcap switch. Providing 35 lumens of light, this flashlight will allow you to make out objects up to 31 meters away, making it handy for household use. In addition, the small size and slim design makes it easy to carry in pocket, purse, toolbox or backpack

### **Product Detail:**

**Designation:** Energizer Value Metal **SAP:** 634041 Colour: Gunmetal Grey Power Source: Two "AA" IEC: LR6 Lamp: Five White LEDs Lamp Life (hr): Lifetime Lamp Output (lumens): 35 Beam Distance (m): 31 Peak Beam Intensity (cd): 80 **Run Time (h:mm):** 1:30 Typical Weight: 34 grams without batteries Dimensions (mm): 23 x 143

#### **Performance:**

2

1

0

On Time (hours)

**Run Time** Continuous Drain to End of Useable Light (21° C)

> AA **Battery Type**

Tested according to ANSI/NEMA FL 1 Standards.

#### **Important Notice**

This datasheet contains information specific to products manufactured at the time of its publication Contents herein do not constitute a claim or warranty ©Energizer / All Rights Reserved



## **ECONOMICAL**

- LEDs never need replacing
- One and a half hours of use between battery changes (with Eveready SHD AA cells)



**Before Using Your Flashlight:** Please read all instructions and cautionary markings on the package and light

## **METAL**

Aluminum casing



