Wireless Compact Desktop Scanner

ADS-1700w

brother
at your side

Its space-saving and portable design, fast scan speed and image optimization features make the Brother ADS-1700W Wireless Desktop Scanner a perfect fit for home or small office use and ideally suited for on-the-go professionals.

- Scan single and double-sided, color and black and white documents in a single pass at up to 25 ppm[1], in a space-saving, portable design

- Easily scan documents, plastic cards, receipts and photos up to 34" in length using the up to 20-page capacity auto document feeder

- Wireless scan to PC, cloud services[4], mobile[3] and network destinations plus USB 3.0 interface for local connections

- The 2.8" color Touchscreen display offers one-touch scanning to preset destinations

- Auto Start Scan lets you drop paper into the feeder to automatically initiate scanning to a predefined profile

- Supports multiple "Scan-to" destinations including File[2], Image[2], OCR[2], Email, Network Folder, Mobile Devices[3] and more to help optimize your business processes

---

Specifications:

Scanner Type	Dual CIS
Standard Interfaces	Wireless 802.11 b/g/n, Micro USB 3.0
Simplex Scan Speeds[1]	Up to 25ppm (color and mono)
Duplex Scan Speeds[1]	Up to 50ipm (color and mono)
Paper Input Capacity	Up to 20 sheets
Document Size (maximum)	8.5" (W) x 34" (L)
Document Size (minimum)	2.0" (W) x 2.76" (L)
LCD Display (size/type)	2.8" color Touchscreen
Scan Resolution (maximum)	Optical: Up to 600 x 600 dpi Interpolated: Up to 1200 x 1200 dpi
Color Bit Depth	48 bit int. / 24 bit ext.
Grayscale Bit Depth	256 levels
Scan to Capability	File[2], Image[2], OCR[2], Email, Email Server[6], Network, FTP, Mobile Devices[3] and USB flash memory drive
Operating System Compatibility	Windows 10, Windows 8/8.1, Windows 7(SP1) Mac® OSX v10.11.6, 10.12.x, 10.3.x Linux
Mobile Device Compatibilty[3]	Brother iPrint&Scan
USB Direct Interface	Yes
Driver Compatibility	TWAIN, WIA, ICA, SANE
Daily Duty Cycle[5]	Up to 1,000 scans/day
Power Source	AC-powered (110-120 V)
Power Consumption	Approx. 9W (Scanning) Approx. 4.5W (Ready Mode) Approx. 1.6W (Sleep Mode)
ENERGY STAR® Certified	Yes
Included Sofware[4]	Power PDF, Nuance® PaperPort® 14 SE, Brother iPrint&Scan
Warranty	1-year limited warranty

Supplies & Accessories*:

PUR-2001C	Pick-up Roller (approx 100,000 scans)♦
SP-2001C	Separation pad (approx 10,000 scans)♦

Carton Contents:

Brother ADS-1700W Scanner

AC Adapter

Quick Setup Guide

Warranty Sheet

Product Registration Sheet

AT YOUR SIDE SUPPORT

At your side support. Online, call, or live chat – free support for the life of your printer. At Brother, we want to ensure that your experience with us is exceptional. Visit us at brother-usa.com where you can download the latest product drivers and software, view product manuals, learn how to get the most out of your product with how-to videos and find answers to frequently asked questions.

Brother Earth
Working with you for a better environment

Working with you for a better environment
At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. **www.brotherearth.com**