


BradyJet J2000 Colour Label Printer

Print eye-catching signs to increase safety and efficiency



www.bradyeurope.com/J2000









The BradyJet J2000 prints on Brady's reliable indoor sign, tag and label materials that stay attached and remain legible when exposed to liquids, alcohol and indoor lighting. They can be counted on to warn coworkers about hazards, or to instruct them on the optimal use or maintenance of machinery.

Signs that comply and get noticed

With over 16 million colour variations, the new BradyJet J2000 enables customers to print their own, eye-catching safety signs, tags, pipe

markers and lean instruction labels to increase workplace safety and efficiency and at the same time comply with any regulatory colour code. Quality images and pictures can be added to any sign thanks to the printer's high, photo-quality printing resolution of 4800 dpi.



Easy to use

With 26.4 by 38.9 cm dimensions, the BradyJet J2000 has a small footprint and is very practical and easy to use. Spring loaded Brady label rolls can be switched in less than 20 seconds and with automatic label set up, the printer is ready to print in no time. And with up to 63.5 mm per second print speed, even larger colour coded sample labels can quickly be printed on demand.



For more information or a live demo, visit www.bradyeurope.com/J2000



Printer specifications

PRINTER					
Description	BradyJet J2000 Colour Label Printer				
Includes	This kit contains a J2000 printer, a power cord and AC adapter, USB cable, a Quick Start Guide, an ink cartridge, a material roll printhead alignment and a Brady Workstation Suite				
Print Speed (mm/sec)	63.5				
Print Technology	Inkjet				
Print Resolution (dpi)	Up to 4800				
Stand-alone Printing (Detached from PC)	Peripheral				
Colour Capability	Full Colour				
Weight (kg)	3.20				
Size W x H x D (mm)	264 x 180 x 389				
Cutter	Auto Cutter				
Warranty	1 year				
MEDIA					
Continuous vs Die-cut Labels	Continuous Tape & Die Cut Labels				
Custom Labels	Yes				
Materials Supported	B-2595, B-2569, B-2551, B-7425J				
Min. Label Length (mm)	6.35				
Min. Label Width (mm)	19				
Max. Label Width (mm)	101.60				
Max. Liner Width (mm)	108.00				
Max. Print Width (mm)	101.60				
Recommended Usage per Day	Around 3000 labels per day, depending on specific label size, text printed and other factors				
SOFTWARE & CONNEC	CTIVITY				
Connectivity Options	USB				
Software Compatibility	Brady Workstation, Windows based driver for 3rd party software use				
COMPLIANCE					
Approval/Compliance	USA: UL, FCC Class A; Canada: cUL, IC/ISED; European Union : CE, RoHS 2011/65/EU, 2014/35/EU, LVD, 2014/30/EU, RED 2014/53/				

EU; Australia/New Zealand : RCM



Printers

Article No.	Order Ref.	Description
150159	J2000-EU	BradyJet J2000 Colour Label Printer - EU
199968	J2000-EU-SFIDS	BradyJet J2000 Colour Label Printer - EU with Brady Workstation SFID Suite
150157	J2000-UK	BradyJet J2000 Colour Label Printer - UK
199969	J2000-UK-SFIDS	BradyJet J2000 Colour Label Printer - UK with Brady Workstation SFID Suite
150162	J2000	BradyJet J2000 Colour Label Printer - US
199972	J2000-US-SFIDS	BradyJet J2000 Colour Label Printer - US with Brady Workstation SFID Suite



The Basic Suite is included with every printer, download it: Workstation.BradyID.com/Free



Create custom signs, labels and pipemarkers with Brady Workstation SFID Suite.

Inks

Article No.	Order Ref.	Description
150154	J20-CMY	CMY pigment based ink cartridge for J2000 Printer

Accessories

Article No.	Order Ref.	Description
150160	J20-CUTTER	Replacement Cutter Blade for J2000
150163	J20-PAD	Replacement Ink Pads for J2000

Materials

		1	1	Label Width	Label Height	Label Length	Total
Diagram	Order Reference	Art. No.	Colour	A (mm)	B (mm)	B (m)	Qty/Pack
Inkjet Receptive Polyester							
∞	J20C-1125-2569	150021	White	29.00	-	30.00	1
∞	J20C-2250-2569	150031	White	57.00	-	30.00	1
∞	J20C-4000-2569	150009	White	101.00	-	30.00	1
A	J20-260-2569	150026	White	55.00	85.00	_	340
A	J20-261-2569	150003	White	75.00	110.00	-	270
A	J20-262-2569	150029	White	105.00	155.00	_	200
Inkjet Rec	Inkjet Receptive Vinyl						
∞	J20C-1125-2595	150010	White	29.00	-	30.00	1
∞	J20C-2250-2595	150014	White	57.00	_	30.00	1
∞	J20C-4000-2595	150017	White	101.00	-	30.00	1
A	J20-260-2595	150013	White	55.00	85.00	-	340
A	J20-261-2595	150027	White	75.00	110.00	-	270
A	J20-262-2595	150032	White	105.00	155.00	-	200
Polyester	with inkjet receptiv	e vinyl top	coat				
∞	J20C-2500-2551	150012	White	64.00	-	15.24	1
∞	J20C-3250-2551	150008	White	83.00	_	15.24	1
	J20-255-2551	150030	White	82.55	146.05	-	100

