

Magellan 9400i Scanner/Scale	
Magellan 9400i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Enhanced Processing with Scale Sentry, EU Power Cord/Brick, RS-232 Std Cable, EAS	941024113-003121
Magellan 9400i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-Up Produce Rail, Enhanced Processing with Scale Sentry, IT/CHI Power Cord/Brick (Cable Sold Separately.)	941024113-00510
Magellan 9400i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Enhanced Processing with Scale Sentry, Retail USB POT Cable	941024113-00053
Magellan 9400i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Enhanced Processing, Retail USB POT Cable	941024112-00053
Magellan 9400i Scanner Only, Std Config, Long Sapphire Platter/Flange Mount w/Fixed Produce Rail, Enhanced Processing, IT/CHI Power Cord/Brick, RS-232 Std Cable, EAS	941015012-005121
Magellan 9400i Scanner Only, Std Config, Med Sapphire Platter/Shelf Mount w/ Flush Top, Enhanced Processing, CSS with Bonnet Mount, Retail USB POT Cable	941014512-03053
Magellan 9400i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Enhanced Processing, Australian Power Cord/Brick, RS-232 Std Cable	941013112-00412
Magellan 9400i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Enhanced Processing, CSS with Bonnet Mount, Retail USB POT Cable	941013112-03053
Magellan 9400i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Enhanced Processing, IT/CHI Power Cord/Brick (Cable Sold Separately.)	941013112-00510
Magellan 9400i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Enhanced Processing, Retail USB POT Cable	941013112-00053
Magellan 9400i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Enhanced Processing/Consolidated Decoding, US Cord/Brick, Retail USB Type A E/P Cable	94101311L-00252
Magellan 9400i Scanner/Scale, Australia Config/Single Interval w/ Dual Display, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Enhanced Processing with Scale Sentry, Retail USB POT Cable	9421140023-040053
Magellan 9400i Scanner/Scale, Australia Config/Single Interval w/ Dual Display, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Enhanced Processing, AU Power Cord/Brick, RS-232 Single Cable	9421140022-040431
Magellan 9400i Scanner/Scale, Canada Metric Config/Single Interval w/ Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, Enhanced Processing, US Std Power Cord/Brick, RS-232 Single Cable	9420450042-020231
Magellan 9400i Scanner/Scale, English Config/Single Interval/No Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, Enhanced Processing with Scale Sentry, CSS with Bonnet Mount, Retail USB POT Cable	9420150013-003053
Magellan 9400i Scanner/Scale, English Config/Single Interval/No Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, Enhanced Processing with Scale Sentry, CSS with Bonnet Mount, US Power Cord/Brick, IBM 46XX Port 9E Cable	9420150013-003242
Magellan 9400i Scanner/Scale, English Config/Single Interval/No Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, Enhanced Processing with Scale Sentry, US Power Cord/Brick, Retail USB Type A E/P Cable	9420150013-000252
Magellan 9400i Scanner/Scale, English Config/Single Interval/No Display, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Enhanced Processing with Scale Sentry, US Power Cord/Brick, Retail USB Type A E/P Cable	9420140013-000252

Magellan 9400i Scanner/Scale, English Config/Single Interval/No Display, Med Sapphire Platter/Shelf Mount w/Fixed Produce Rail, Enhanced Processing/Consolidated Decoding, US Power Cord/Brick, Retail USB POT Cable	942014001L-000253
Magellan 9400i Scanner/Scale, EU Factory Pre-Verified Metric Config/Dual Interval/Single Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Enhanced Processing, EU Power Cord/Brick, RS-232 WN Cables, EAS	9460441322-2203211
Magellan 9400i Scanner/Scale, EU Factory Pre-Verified Metric Config/Single Interval w/ Display, Long Sapphire Platter/Flange Mount w/Flip-up Produce Rail, Enhanced Processing with Scale Sentry/Consolidated Decoding, EU Power Cord/Brick, RS-232 Cable, EAS	946035103M-0003311
Magellan 9400i Scanner/Scale, EU Factory Pre-Verified Metric Config/Single Interval/Dual Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Enhanced Processing with Scale Sentry, EU Power Cord/Brick, RS-232 Single Cable	9460441033-040331
Magellan 9400i Scanner/Scale, EU Factory Pre-Verified Metric Config/Single Interval/Single Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Enhanced Processing with Scale Sentry, EU Power Cord/Brick, EAS (Cable Sold Separately.)	9460441033-0203101
Magellan 9400i Scanner/Scale, Metric Config/Single Interval w/Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, Enhanced Processing with Scale Sentry/Consolidated Decoding, Retail USB POT Cable, EAS	942045011M-0200531
Magellan 9400i Scanner/Scale, Metric Config/Single Interval/No Display, Long Sapphire Platter/Flange Mount w/Fixed Produce Rail, Enhanced Processing with Scale Sentry/Consolidated Decoding, US Power Cord/Brick, Retail USB Type A E/P Cable, EAS	942035011M-0002521
Magellan 9400i Scanner/Scale, Metric Config/Single Interval/No Display, Med Sapphire Platter/Shelf Mount w/Fixed Produce Rail, Enhanced Processing with Scale Sentry/Consolidated Decoding, CSS with Bonnet Mount, US Power Cord/Brick, Retail USB Type A E/P	942034010M-003252

EASEOFCARE AGREEMENTS	
MAG9400i, SCANNER ONLY, 2 DAYS, 3 YEARS, COMPREHENSIVE	ZSC2M94NS31
MAG9400i, SCANNER ONLY, 2 DAYS, 5 YEARS, COMPREHENSIVE	ZSC2M94NS51
MAG9400i, SCANNER ONLY, 2 DAYS, RENEWAL, COMPREHENSIVE	ZSC2M94NSR1
MAG9400i, SCANNER ONLY, 5 DAYS, 3 YEARS	ZSN5M94NS31
MAG9400i, SCANNER ONLY, 5 DAYS, 5 YEARS	ZSN5M94NS51
MAG9400i, SCANNER ONLY, MINIMUM REPAIR CHARGE	ZR0M94SOMIN
MAG9400i, SCANNER ONLY, OVERNIGHT, 3 YEARS, COMPREHENSIVE	ZSC1M94NS31
MAG9400i, SCANNER ONLY, OVERNIGHT, 5 YEARS, COMPREHENSIVE	ZSC1M94NS51
MAG9400i, SCANNER ONLY, OVERNIGHT, RENEWAL, COMPREHENSIVE	ZSC1M94NSR1
MAG9400i, SCANNER ONLY, WHOLE UNIT REPAIR	ZR0M94SOMAX
MAG9400i, SCANNER ONLY. 5 DAYS, RENEWAL	ZSN5M94NSR1
MAG9400i, SCANNER SCALE, 2 DAYS, 3 YEARS, COMPREHENSIVE	ZSC2M94SS31
MAG9400i, SCANNER SCALE, 2 DAYS, 5 YEARS, COMPREHENSIVE	ZSC2M94SS51
MAG9400i, SCANNER SCALE, 2 DAYS, RENEWAL, COMPREHENSIVE	ZSC2M94SSR1

MAG9400i, SCANNER SCALE, 5 DAYS, 5 YEARS	ZSN5M94SS51
MAG9400i, SCANNER SCALE, 5 DAYS, RENEWAL	ZSN5M94SSR1
MAG9400i, SCANNER SCALE, MINIMUM REPAIR CHARGE	ZR0M94SSMIN
MAG9400i, SCANNER SCALE, OVERNIGHT, 5 YEARS, COMPREHENSIVE	ZSC1M94SS51
MAG9400i, SCANNER SCALE, OVERNIGHT, RENEWAL, COMPREHENSIVE	ZSC1M94SSR1
MAG9400i, SCANNER SCALE, WHOLE UNIT REPAIR	ZR0M94SSMAX
MAGELLAN 9400i SCANNER SCALE, OVERNIGHT, 3 YEARS, COMPREHENSIVE	ZSC1M94SS31

CABLES	
Cable IBM 4683, Port 17, POS, 4.5 m/15 ft	90A052131
CABLE, EAS, INTERLOCK, 1800MM	90A052247
Cable, IBM 46XX, Port 9E, 4.5 m/15 ft	90A052132
Cable, IBM USB, External Power, 4.5 m/15 ft	90A052133
Cable, IBM USB, POT, 3 PIN, 4.6M	90A052276
Cable, RS-232, 9D, Beetle, 4.5 m/15 ft	90A052129
Cable, RS-232, ICL, PC, 9D,4.5 m/15 ft	90A052121
Cable, RS-232, PC Scale, Female, 15 ft	90A052138
Cable, RS-232, PC, 25D,4.5 m/15 ft	90A052125
Cable, RS-232, SASI, Super Star, 15 ft	90A052137
Cable, RS-232, SASI, Super Star, RJ4, 15 ft	90A052122
Cable, RS-232, SNI Beetle, 4.5 m/15 ft	90A052197
Cable, USB, Type A, External Power, 4.5 m/15 ft	90A052135

MISCELLANEOUS		
	Customer Service Scanner (Mount Ordered Separately.)	90ACC0169
	Customer Service Scanner with Bonnet Back Mount Accessory	90ACC0175
	Customer Service Scanner with Bonnet Side Mount Accessory	90ACC0174
	Customer Service Scanner with Omni Mount Accessory	90ACC0170
Platter, Scanner Only, Long, Sapphire Glass, Fixed Produce Rail, Mgl 9400i		90ACC0275
Platter, Scanner Only, Long, Sapphire Glass, Flip Up Produce Rail, Mgl 9400i		90ACC0276
Platter, Scanner Only, Long, Sapphire Glass, Flush Top, Mgl 9400i		90ACC0277
Platter, Scanner Only, Medium, Sapphire Glass, Fixed Produce Rail, Mgl 9400i		90ACC0272
Platter, Scanner Only, Medium, Sapphire Glass, Flip Up Produce Rail, Mgl 9400i		90ACC0273
Platter, Scanner Only, Medium, Sapphire Glass, Flush Top, Mgl 9400i		90ACC0274
Platter, Scanner Only, Short, Sapphire Glass, Mgl 9400i		90ACC0255
Platter, Scanner/Scale, Long, Sapphire Glass, Fixed Produce Rail, Mgl 9400i		90ACC0262
Platter, Scanner/Scale, Long, Sapphire Glass, Fixed Produce Rail, with Scale Sentry, Mgl 9400i		90ACC0261
Platter, Scanner/Scale, Long, Sapphire Glass, Flip Up Produce Rail, Mgl 9400i		90ACC0264
Platter, Scanner/Scale, Long, Sapphire Glass, Flip Up Produce Rail, with Scale Sentry, Mgl 9400i		90ACC0263
Platter, Scanner/Scale, Long, Sapphire Glass, Flush Top, Mgl 9400i		90ACC0265
Platter, Scanner/Scale, Medium, Sapphire Glass, Fixed Produce Rail, Mgl 9400i		90ACC0257
Platter, Scanner/Scale, Medium, Sapphire Glass, Fixed Produce Rail, with Scale Sentry, Mgl 9400i		90ACC0256
Platter, Scanner/Scale, Medium, Sapphire Glass, Flip Up Produce Rail, Mgl 9400i		90ACC0259

Platter, Scanner/Scale, Medium, Sapphire Glass, Flip Up Produce Rail, with Scale Sentry, Mgl 9400i	90ACC0258
Platter, Scanner/Scale, Medium, Sapphire Glass, Flush Top, Mgl 9400i	90ACC0260
Scale Zero Button, Magellan 9300i/9400i	90ACC0393

MOUNTS/STANDS		
	Bonnet Back Mount for Customer Service Scanner (CSS Ordered Separately)	90ACC0172
	Bonnet Side Mount for Customer Service Scanner (CSS Ordered Separately)	90ACC0171
	Omni Mount for Customer Service Scanner (CSS Ordered Separately)	90ACC0173

POWER SUPPLIES/CORDS	
Power Brick, Worldwide	90ACC0194
Power Cord, 100V, Japan	6003-0927
Power Cord, 120V, US, Twist & Lock	6003-0932
Power Cord, 220V, Australia	6003-0925
Power Cord, 220V, Italy/Chile	6003-0924
Power Cord, 240V, UK	6003-0923
Power Cord, AC, IEC/EU	6003-0940
Power Cord, Euro Monitor	6003-0931
Power Cord, IEC C13, Brazil (For use with 8-0935)	6003-0942
US Power Cord, 110V, US, Standard	6003-0941

REMOTE SCALE DISPLAYS		
	Kit, Remote Scale Display, English, Dual Head, Dual Interval, US/Canada/Puerto Rico	90ACC0107
	Kit, Remote Scale Display, English, Dual Head, Single Interval, US/Canada/Puerto Rico	90ACC0103
	Kit, Remote Scale Display, English, Single Head, Dual Interval, US/Canada/Puerto Rico	90ACC0106
	Kit, Remote Scale Display, English, Single Head, Single Interval, US/Canada/Puerto Rico	90ACC0102
	Kit, Remote Scale Display, Metric, Dual Head, Dual Interval, Europe	90ACC0109
	Kit, Remote Scale Display, Metric, Dual Head, Single Interval, Europe	90ACC0105
	Kit, Remote Scale Display, Metric, Single Head, Dual Interval, Europe	90ACC0108
	Kit, Remote Scale Display, Metric, Single Head, Single Interval, Europe	90ACC0104