Power supply



FEATURES:


Switching; wide input voltage range, small dimensions and low weight
Output protected against short circuits and over-voltage
Mains lead set not included

SPECIFICATION:

Output voltage	12 VDC
Output current	2.5 A
Power	30.0 W
Input voltage	100240 VAC
Connection, secondary side	2.5 x 5.5 mm Barrel Plug
Polarity	+(C)
Connection, primary side	2-pin C8 socket



Art. Nr. SA130D-12U 2,5MM



UL 1185 AWG18 80°C

