Desk-top cases - ratiopacPRO / -air

Guide rails for plug-in units and modules, one-piece, groove width 2 mm and 2.5 mm

Order Information

Assembly

- can be clipped into Al extruded horizontal rails

can be clipped into 1.5 mm thick

Storage temperature


from -40 °C ... 130 °C

For plug-in units and frame type plug-in units

Standard



Up to 220 mm length, PBT, UL 94 V-0; from 280 mm length, multi-piece, end piece PBT, UL 94 V-0, central section Al extrusion



PBT, UL 94 V-0, red, connector is clipped directly onto the guide rails; for euroboards 100 x 160 mm or 100 x 220 mm only

06101501

With DIN connector fixing as standard

Board lengths	Groove width	Colour		
mm	mm	mm	PU 10 pieces ²⁾	1 pair (SPQ 10) ¹⁾
70	2	red	_	_
70	2	grey	-	_
160	2	red	24560-351	64560-074
220	2	red	24560-353	64560-075
280	2	red	24560-379	-
340	2	red	24560-380	_
160	2.5	red	-	-
220	2.5	red	-	_

Accessories

Retention screw, PU 100 pieces	24560-141			
ESD clip, PU 50 pieces	24560-255			
1) SPO (standard pook quantity). Order number includes 1 piece, but delivery is evaluatively made in standard pook quantity (SPO); places order at least the SPO quantity or				

Q (standard pack quantity): Order number includes 1 piece, but delivery is exclusively made in standard pack quantity (SPQ); please order at least the SPQ quantity a multiple thereof

Description of accessories see from page 6.41

²⁾ Part no. includes one packing unit (PU); delivery is exclusively made in PU