ALPHA

3470UFR125P62 blue

EAN 4031582304442

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, dustguard, plate fitting. Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, roller bearing





Picture may differ from original product


Technical Data

Wheel diameter	125 mm
Width of Tread	40 mm
Size of Plate	105 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Offset	40 mm
Swivel Interference	205 mm
Overall height	155 mm
Temperature	- 20 / + 80 °C
Standard	EN 12532
Weight	1.084 kg
Swivel Radius	102.5 mm
Hardness of tread	Shore A 64
Load capacity	250 kg
Load capacity (static)	500 kg


Advantages at a glance

Roll performance	• • • 0 0
Movement noise	• • • •
Attrition	• • • 0 0
Corrosion resistance	• • • 0 0

Dimensions



Structure & Mounting



ALPHA

3470UFR125P62 blue

EAN 4031582304442

Structure & Mounting

