

EAN 4031582070392

Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, roller bearing






Picture may differ from original product

Dimensions

Technical Data

Wheel diameter	100 mm
Width of Tread	34 mm
Axle Hole-Ø	12 mm
Hub length	44.4 mm
Temperature	- 20 / + 80 °C
Standard	EN 12532
Weight	0.249 kg
Hardness of tread	Shore A 64
Load capacity	160 kg
Load capacity (static)	320 kg



Advantages at a glance

Roll performance	
Movement noise	• • • • •
Attrition	$\bullet \bullet \bullet \circ \circ$
Corrosion resistance	$\bullet \bullet \bullet \circ \circ$