



PCle Gen3.0 SSD for Mac®

JetDrive[™] 825

Transcend's JetDrive 825 Thunderbolt™ PCle portable SSD combines a JetDrive 820 PCle SSD with a sleek aluminum Thunderbolt enclosure to instantly revitalize your Thunderbolt-equipped MacBook Pro, MacBook Air, Mac mini, or Mac Pro!



Thunderbolt technology in a sleek case

Transcend's JetDrive 825 features a 10Gb/s Thunderbolt interface, capable of blazing-fast file transfers. The drive is housed in sleek, aluminum alloy enclosure which was designed to tastefully complement your Mac's simple, clean design. In addition, the inner SSD is removable for greater ease of use based on users' preferences.



Expand storage in a flash

Upgrading your Mac with a Transcend JetDrive 820 allows you to increase storage capacity to up to 960GB, ensuring you have plenty of space for your documents, photos, music, and videos.



Feel the need for speed

Transcend's JetDrive 820 utilizes the PCIe™ Gen3 x2 interface paired with the latest 3D NAND flash, resulting in compelling performance of up to 950MB/s read and 950MB/s write.

Transcend's JetDrive 820 gives you fluid, real-time performance for professional tasks, video editing, and 3D graphics.





PCle Gen3.0 SSD for Mac®

JetDrive[™] 825

Features

- Compatible with MacBook Air 11" & 13"
 (Mid 2013 2017), MacBook Pro Retina®
 13" & 15" (Late 2013 Mid 2015), Macmini (Late 2014), and Mac Pro (Late 2013)
- · Up to 950 MB/s read; 950 MB/s write
- JetDrive 820 AHCI PCIe Gen3 x2 SSD inside a Thunderbolt enclosure
- · Installation tools included
- Free download of the JetDrive Toolbox software

Transcend

JetDrive Toolbox

JetDrive Toolbox is designed for Transcend's Apple Solutions including JetDrive SSDs, JetDrive Lite expansion cards, and JetDrive Go flash drives. The software helps maintain a healthy SSD by keeping it up-to-date and preventing problems before they occur.

Specifications

Α	n	n	Р	а	r	а	n	C	0
\neg	v	\sim		ч		ч		~	C

Dimensions	120 mm x 31.5 mm x 18.2 mm (4.72" x 1.24" x 0.72")		
Weight	88 g (3.10 oz)		

Interface

Connection Interface	Thunderbolt 10 Gb/s
Bus Interface	AHCI PCIe Gen3 x2

Storage

Flash Type	3D NAND flash
Capacity	240 GB / 480 GB / 960 GB

Operating Environment

Note	• Performance tested with AJA v1.0 / Black Magic v3.1.			
Operating Voltage	15V			
Storage Temperature	-40°C (-40°F) ~ 85°C (185°F)			
Operating Temperature	0°C (32°F) ~ 60°C (140°F)			

Performance

Read Speed (Max.)	950 MB/s
Write Speed (Max.)	950 MB/s
Note	 Speed may vary due to host hardware, software, usage, and storage capacity. The 1TB native SSD is not compatible with the JetDrive 855 and JetDrive 825's enclosure as its dimensions are designed larger than other capacities.

Warranty

Certificate	CE / FCC / BSMI / EAC
Warranty	Five-year Limited Warranty

Ordering Information

240GB	TS240GJDM825
480GB	TS480GJDM825
960GB	TS960GJDM825

Product specifications are subject to change without notice. Pictures shown may differ from actual products. When used as a storage capacity unit, one terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment.