

# Performance C Series

### AMD CPU Cooler A404T

Widening the Performance C CPU cooler Series, Xilence now launches the A404T AMD – a compact but high-performance top-flow cooler for powerful multi-core processors. The cooler scores with a silent 92mm fan and an innovative fin design allowing an easier circulation of air through the reams of fins. Thus, the speed of the PWM-regulated 92mm fan can be kept at an especially low level. Thanks to the heat pipes being in direct contact to the CPU, the heat transition between CPU and cooler proves to be very smooth and efficient.



#### **Product Features**

- Silent hydro bearing 92 mm PWM fan
- Four 6mm copper heat pipes for a maximum heat dissipation
- Light aluminum heat sink
- Suitable for AMD sockets AM4/AM3/AM2/AM2+/FM2+/FM2/FM1
- Thermal paste included

#### Technical Data

Sockets AM4/AM3/AM2/AM2+/FM2+/FM2/FM1

CPU max. Watt 125W

Fan Size 92 x 92 x 25mm

Fan Speed  $600-2200 \pm 10\%$  RPM

Air Flow 65.4 CFM Fan Control PWM

Noise Level 14 - 21.8 dB (A)

Thermal Paste included

Dimensions 105 x 100 x 55mm

Weight 306g

## Logistical Data

Manufacturer Number A404T Item Number XC040

EAN Barcode 4044953501173







