

3930TSP

TRUCKSTAR PRO | Signal lamps



Product benefits

- Tried and trusted in millions of vehicles of well-known automobile manufacturers
- Excellent price/performance ratio
- Impressive brightness and reliable lifetime
- Up to 100 % longer lifetime (compared to standard lamps)
- Suitable for heavy duty applications thanks to very high vibration resistance



Product datasheet

Technical data


Electrical data


Power input	5 W
Nominal voltage	24.0 V
Nominal wattage	4.00 W
Power input tolerance	±10 %
Test voltage	28.0 V

Photometrical data

Luminous flux	35 lm
Luminous flux tolerance	±20 %

Dimensions & weight





IEC 7005-12 DIN 49642 T 12

Length	27.4 mm
Diameter	9 mm
Product weight	2.03 g

Lifespan

Lifespan B3	550 h
Lifespan Tc	1000 h

Additional product data

Certificates & standards


ECE category	T4W
--------------	-----

Country specific categorizations

Product datasheet

Order reference	3930TSP
Order reference	373013F

Product datasheet



Others graphics

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321174055	3930TSP	Blister 2	93 mm x 15 mm x 58 mm	0.08 dm ³	15.06 g
4008321174062	3930TSP	Shipping carton box 20	146 mm x - x 106 mm	2.24 dm ³	197.67 g
4008321795106	3930TSP	Unpacked 1	14 mm x 6 mm x 9 mm	0.00 dm ³	11.00 g
4008321795113	3930TSP	Folding carton box 10	46 mm x 29 mm x 112 mm	0.15 dm ³	31.30 g
4008321795120	3930TSP	Shipping carton box 50	148 mm x - x 55 mm	0.94 dm³	186.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Legal advice

ECE E1 approval

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.