

## devolo Magic 2 WiFi 6

The Magic 2 WiFi 6 revolutionises the Wi-Fi speed in your home! With 50 percent more Wi-Fi power than any Wi-Fi 5 PLC adapter, it reaches speeds of up to 1800 Mbps and makes this speed available to every user. Thanks to OFDMA, the channels are used with flexibility: Top-notch Wi-Fi for everyone – when sending or receiving and even when there are many users in parallel!

Your Internet signal is distributed over Powerline technology at speeds of up to 2400 Mbps, directly over the electrical wiring and to any room. An adapter turns any power socket into an access point for high-performance multi-room Wi-Fi. And multiple devolo Magic adapters connect to each other automatically to form a comprehensive mesh network.

For maximum connectivity, Magic 2 WiFi 6 is also equipped with two Gigabit LAN ports. It is the world's fastest Powerline adapter and its top-notch features make it a networking powerhouse for your home. Enjoy powerful mesh Wi-Fi throughout the home – for everyone!



Wi-Fi with Mesh

**OFDMA and MU-MIMO Technology** 

Up to 2400 Mbps

2x Gigabit LAN

Range up to 500 meters





### devolo Magic 2 WiFi 6

#### Why this product?

- 50% better Wi-Fi performance than any Wi-Fi 5 PLC adapter: up to 1800 Mbps! The latest technology of the Magic 2 WiFi 6 supplies your mobile devices with an extremely strong Wi-Fi signal.
- Faster and more responsive: Simultaneous sending and receiving at lightning speed.
- Extra power for lots of users: Mesh Wi-Fi for everyone at the same time and throughout the home! Thanks to efficient utilisation of the frequency spectrum.

#### Why devolo Magic?

- Powerline is the best Wi-Fi solution: The Internet is transmitted to any room through ceilings and walls over the electrical wiring and with a Wi-Fi adapter any power socket becomes a powerful hotspot. More reliable than any repeater!
- Future-proof thanks to G.hn and WiFi 6: Rely on cutting-edge technology that will give you extremely high speeds, increase your stability and boost your range.
- Maximum security: devolo products are in line with the most recent encryption standards (WPA2/WPA3), ensuring that your data is secure (banking standard).

#### Why devolo?

- Cutting-edge technology from Germany: devolo has been developing standard-setting products since 2002 for millions of customers around the world. devolo products have received more than 600 awards.
- Control using the devolo Home Network app: Set up parental controls, guest Wi-Fi and time control settings with ease!
- Our promise: 3-year manufacturer's warranty.

**Wi-Fi Upgrade:** It's very easy to replace and disable your old router Wi-Fi with this set – for maximum Wi-Fi power throughout the home.





devolo Magic 2 WiFi 6 Mesh Starter Kit: Art. -Nr.: 08932 (NL, ES, EU)



devolo Magic 2 WiFi 6 Mesh Multiroom Kit: Art. -Nr.: 08936 (NL, ES, EU)



devolo Magic 2 WiFi 6 Add-On:

Art. -Nr.: 08811 (DE, AT, NL, ES, PT, EU)



devolo Magic 2 WiFi 6 Starter Kit:

Art. -Nr.: 08822 (ES, PT, EU)



devolo Magic 2 WiFi 6 Multiroom Kit:

Art -Nr : 08830 (FS PT FU)



## devolo Magic 2 WiFi 6

# **Technical Data**







Steering



2400 Mbps

2 x Gigabit

Ethernet







Integrated

Multi-User-

MIMO



#### Ports

Ethernet	2x RJ45
Integrated Socket	Type F (CEE 7/4) Ampacity: 16A Type E (CEE 7/5) Ampacity: 15A Type G (BS1363) Ampacity: 13A Type J (SEV 1011) Ampacity: 10A Network filter (2-80 MHz, -22 db to -45 db)
Plug	Type F (CEE 7/4)  Type E+F (CEE 7/7)  Type G (BS1363)  Type J (SEV 1011)

#### Wi-Fi

Standards	Wi-Fi 4/5/6 (IEEE 802.11 a/b/g/n/ac/ax/k/v/r)					
Radios	2,4GHz + 5GHz Dual Band Dual concurrent					
Channels	2,4 GHz 1-13  5 GHz 36-48 (Indoor)  52-64 (DFS+TPC)  100-140 (DFS+TPC)					
Channel widths	20/40/80 MHz					
Streams	2x2 MIMO					
Data rates	2,4 GHz up to 574 Mbps 5 GHz up to 1201 Mbps					
Mode	Access Point					

#### **Powerline**

Standards	G.hn (HomeGrid Forum)
Transmission speeds	2400 Mbps (MIMO) 1200 Mbps (SISO)
Range	500 m
Transmission frequency	2-86 MHz
Mode	Peer to Peer



#### **Ethernet**

Standards	IEEE 802.3 u/ab/x/az
Transmission speeds	10/100/1.000 Mbps
Auto MDI-X	Yes
QoS	Yes
IPv4 / IPv6	Yes / Yes

#### **Buttons/LEDs**

WLAN (Button/LED)	Wi-Fi on/off WPS
Home (Button/LED)	Powerline connection
Reset (Button)	Reboot Reset Settings
LEDs switchable	Yes

#### **Software Features**

Guest Wi-Fi	Yes
Wi-Fi timing	Yes
Parental lock	Yes
Mesh Wi-Fi	Yes
Airtime Fairness	Yes
Access Point Steering	Yes
Wi-Fi encryption	WPA/WPA2/WPA3 Personal
WPS	PBC, PIN

#### Administration

Device website	Yes (Internet browser)
Home Network App	Yes (iOS/Android)
Cockpit software	Yes (Windows/MacOS/Linux)

#### **Environment and physical data**

Power consumption	Maximum: 12,4 W Typcial: 8,2 W Stand-By: 2,5 W
Power supply	196-250 V AC (50 Hz)
Temperature (Storage • Operating)	-25°C to 70°C • 0°C to 40°C
Dimensions (in mm, without socket)	152 x 76 x 40
Ambient conditions	10-90% Humidity (non-condensing)



## Sales information

Warranty	v (in vears)	3

Documentation: Printed Install Flyer Accessories

Ethernet cable RJ45-RJ45











	Add-on adapter 08811 (DE, AT, NL, ES, PT, EU)	Starter Kit 08822 (ES, PT, EU)	Multiroom Kit 08830 (ES, PT, EU)	Mesh Starter Kit 08932 (NL, ES, EU)	Mesh Multiroom Kit 08936 (NL, ES, EU)
EAN	4250059688117	4250059688223	4250059688308	4250059689329	4250059689367
Weight	584 g	904 g	1293 g	1080 g	1470 g
Dimensions	190 x 118 x 92 mm	188 x 231 x 92 mm	188 x 231 x 92 mm	188 x 231 x 92 mm	188 x 231 x 92 mm

#### **WEEE** additional information

Weight WEEE	374 g	640 g	1014 g	790 g	1165 g
Paper (Der Grüne Punkt)	175 g	225 g	240 g	225 g	240 g
Plastic (Der Grüne Punkt)	2 g	4 g	6 g	4 g	6 g
other (Der Grüne Punkt)	0 g	0,2 g	0,2 g	0,2 g	0,2 g